

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251278

Luminaire Tested: **LSR8B60D010 EC8B60940 8LBM0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251278
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201629)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60940 8LBM0GPH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 4000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4891.0 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251278

CATALOG NUMBER: LSR8B60D010 EC8B60940 8LBM0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P251278

CATALOG NUMBER: LSR8B60D010 EC8B60940 8LBM0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	191312
5°	186455
10°	167187
15°	148872
20°	135836
25°	123358
30°	101166
35°	66615
40°	33193
45°	12341
50°	3756
55°	425
60°	259
65°	0
70°	180
75°	727
80°	0
85°	708



TEST NUMBER: P251278

CATALOG NUMBER: LSR8B60D010 EC8B60940 8LBM0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	552.3	11.3
10°-20°	1313.2	26.8
20°-30°	1635.7	33.4
30°-40°	1103.8	22.6
40°-50°	260.9	5.3
50°-60°	18.9	0.4
60°-70°	3.3	0.1
70°-80°	2.4	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3501.2	71.6
0°-40°	4605.0	94.2
0°-60°	4884.8	99.9
0°-90°	4891.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4891.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6204	
5°	6024	552
15°	4663	1313
25°	3626	1636
35°	1770	1104
45°	283	261
55°	8	19
65°	0	3
75°	6	2
85°	2	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251278

CATALOG NUMBER: LSR8B60D010 EC8B60940 8LBM0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	6204.1
2.5°	6194.2
5°	6023.6
7.5°	5716.5
10°	5339.4
12.5°	4980.2
15°	4663.3
17.5°	4390.1
20°	4139.4
22.5°	3896.6
25°	3625.6
27.5°	3272.5
30°	2841.2
32.5°	2319.5
35°	1769.6
37.5°	1266.3
40°	824.6
42.5°	493.5
45°	283.0
47.5°	158.6
50°	78.3
52.5°	36.1
55°	7.9
57.5°	2.0
60°	4.2
62.5°	6.1
65°	0.0
67.5°	4.2
70°	2.0
72.5°	2.0
75°	6.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	2.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251278

CATALOG NUMBER: LSR8B60D010 EC8B60940 8LBM0GPH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)