

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244027

Luminaire Tested: **LSR8B15D010 EC8B15835 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244027
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15835 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1726.0 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244027

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P244027

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88	91	88	86	88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63	71	66	62	69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47	56	51	46	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29674
5°	29803
10°	30288
15°	31053
20°	31595
25°	31632
30°	30654
35°	28064
40°	24390
45°	19301
50°	12516
55°	6252
60°	2627
65°	1153
70°	361
75°	179
80°	178
85°	177



TEST NUMBER: P244027

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBS0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.0	5.3
10°-20°	274.9	15.9
20°-30°	425.8	24.7
30°-40°	462.4	26.8
40°-50°	336.1	19.5
50°-60°	114.2	6.6
60°-70°	18.2	1.1
70°-80°	2.0	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	792.8	45.9
0°-40°	1255.2	72.7
0°-60°	1705.5	98.8
0°-90°	1726.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1726.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	962	
5°	963	92
15°	973	275
25°	930	426
35°	746	462
45°	443	336
55°	116	114
65°	16	18
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P244027

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBS0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	962.3
2.5°	962.3
5°	962.8
7.5°	964.3
10°	967.3
12.5°	970.8
15°	972.7
17.5°	970.8
20°	962.8
22.5°	948.5
25°	929.7
27.5°	901.5
30°	860.9
32.5°	806.9
35°	745.5
37.5°	678.7
40°	605.9
42.5°	527.2
45°	442.6
47.5°	351.5
50°	260.9
52.5°	178.7
55°	116.3
57.5°	70.8
60°	42.6
62.5°	26.2
65°	15.8
67.5°	8.9
70°	4.0
72.5°	2.5
75°	1.5
77.5°	1.0
80°	1.0
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)