

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245551

Luminaire Tested: **LSR8B15D010 EC8B15850 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245551
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15850 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1396.0 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245551

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245551

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66	74	70	66	73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51	60	55	51	59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33519
5°	32728
10°	31700
15°	31244
20°	30876
25°	30210
30°	28297
35°	23106
40°	13795
45°	8286
50°	5973
55°	4064
60°	2547
65°	1248
70°	316
75°	119
80°	89
85°	0



TEST NUMBER: P245551

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	7.1
10°-20°	276.2	19.8
20°-30°	405.6	29.1
30°-40°	367.7	26.3
40°-50°	157.4	11.3
50°-60°	69.6	5.0
60°-70°	18.6	1.3
70°-80°	1.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	781.2	56.0
0°-40°	1148.9	82.3
0°-60°	1375.9	98.6
0°-90°	1396.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1396.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1087	
5°	1057	99
15°	979	276
25°	888	406
35°	614	368
45°	190	157
55°	76	70
65°	17	19
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P245551

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1087.0
2.5°	1078.4
5°	1057.3
7.5°	1033.1
10°	1012.4
12.5°	995.3
15°	978.7
17.5°	961.0
20°	940.9
22.5°	917.2
25°	887.9
27.5°	848.6
30°	794.7
32.5°	719.1
35°	613.8
37.5°	475.7
40°	342.7
42.5°	247.4
45°	190.0
47.5°	153.2
50°	124.5
52.5°	98.8
55°	75.6
57.5°	56.4
60°	41.3
62.5°	28.7
65°	17.1
67.5°	7.6
70°	3.5
72.5°	2.0
75°	1.0
77.5°	0.5
80°	0.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)