

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246595

Luminaire Tested: **LSR8B15D010 EC8B15927 8LBW0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246595
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15927 8LBW0MW
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 2700 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1226.2 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246595

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246595

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84		88	85	82		86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59		68	63	59		67	62	58	56
6	79	67	60	54	77	66	59	54	65	58	54		63	58	53		62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49		59	53	49		57	52	48	47
8	69	58	50	45	68	57	50	45	56	50	45		55	49	45		54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P246595

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBW0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.9	6.1
10°-20°	206.2	16.8
20°-30°	302.4	24.7
30°-40°	276.4	22.5
40°-50°	136.8	11.2
50°-60°	101.2	8.3
60°-70°	77.8	6.3
70°-80°	40.5	3.3
80°-90°	10.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	583.4	47.6
0°-40°	859.8	70.1
0°-60°	1097.8	89.5
0°-90°	1226.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1226.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	812	
5°	796	75
15°	730	206
25°	662	302
35°	459	276
45°	166	137
55°	112	101
65°	79	78
75°	38	41
85°	8	10
90°	0	



TEST NUMBER: P246595

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBW0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	812.5
2.5°	808.2
5°	795.7
7.5°	779.1
10°	762.0
12.5°	745.2
15°	730.0
17.5°	715.6
20°	700.1
22.5°	682.5
25°	661.9
27.5°	633.6
30°	593.9
32.5°	538.3
35°	458.6
37.5°	359.8
40°	265.6
42.5°	201.0
45°	166.0
47.5°	147.0
50°	133.0
52.5°	121.7
55°	112.0
57.5°	103.8
60°	96.9
62.5°	89.4
65°	79.3
67.5°	68.4
70°	57.6
72.5°	47.5
75°	37.7
77.5°	29.1
80°	21.4
82.5°	14.7
85°	8.5
87.5°	3.2
90°	0.0

(END OF REPORT)