

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250862

Luminaire Tested: **LSR8B60D010 EC8B609730 8LBMOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B609730 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4766.0 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250862

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P250862

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72		79	75	72		77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68		75	71	68		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58		65	61	58		64	60	58	56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250862

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	727.5	15.3
10°-20°	1526.4	32.0
20°-30°	1493.6	31.3
30°-40°	826.4	17.3
40°-50°	159.9	3.4
50°-60°	24.5	0.5
60°-70°	6.0	0.1
70°-80°	1.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3747.6	78.6
0°-40°	4573.9	96.0
0°-60°	4758.4	99.8
0°-90°	4766.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4766.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8314	
5°	7927	728
15°	5497	1526
25°	3262	1494
35°	1301	826
45°	183	160
55°	22	25
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P250862

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8314.2
2.5°	8199.9
5°	7926.6
7.5°	7543.4
10°	6976.0
12.5°	6258.7
15°	5496.8
17.5°	4782.4
20°	4188.3
22.5°	3696.7
25°	3261.5
27.5°	2851.6
30°	2415.0
32.5°	1902.6
35°	1301.0
37.5°	782.7
40°	458.9
42.5°	286.6
45°	182.7
47.5°	114.4
50°	66.8
52.5°	37.1
55°	22.3
57.5°	13.4
60°	10.4
62.5°	7.4
65°	5.9
67.5°	4.5
70°	3.0
72.5°	1.5
75°	1.5
77.5°	1.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)