

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246289

Luminaire Tested: **LSR8B15D010 EC8B15935 8LBW0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246289  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B15D010 EC8B15935 8LBW0B  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 3500 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 847.0 lumens  
Efficiency: N/A  
Efficacy: 58.8 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246289

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBW0B

### Luminous Intensity Polar Plot





TEST NUMBER: P246289

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBW0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  | 0   |     |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 113 | 110 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 102 | 101 |  | 101 | 99  | 98  |  | 97  | 96  | 95  | 93  |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 97  | 94  | 92  |  | 94  | 92  | 90  |  | 92  | 90  | 88  | 86  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 85  | 91  | 87  | 84  |  | 89  | 85  | 82  |  | 86  | 84  | 81  | 80  |
| 4   | 96  | 88  | 83  | 78  | 94  | 87  | 82  | 78  | 85  | 80  | 77  |  | 83  | 79  | 76  |  | 81  | 78  | 75  | 74  |
| 5   | 91  | 82  | 76  | 72  | 89  | 81  | 76  | 71  | 80  | 75  | 71  |  | 78  | 74  | 70  |  | 76  | 73  | 70  | 68  |
| 6   | 86  | 77  | 71  | 66  | 85  | 76  | 70  | 66  | 74  | 69  | 65  |  | 73  | 68  | 65  |  | 72  | 68  | 65  | 63  |
| 7   | 82  | 72  | 66  | 61  | 80  | 71  | 65  | 61  | 70  | 64  | 61  |  | 69  | 64  | 60  |  | 67  | 63  | 60  | 58  |
| 8   | 77  | 67  | 61  | 57  | 76  | 67  | 61  | 57  | 66  | 60  | 56  |  | 65  | 60  | 56  |  | 64  | 59  | 56  | 54  |
| 9   | 73  | 63  | 57  | 53  | 72  | 63  | 57  | 53  | 62  | 56  | 52  |  | 61  | 56  | 52  |  | 60  | 55  | 52  | 51  |
| 10  | 70  | 59  | 53  | 49  | 68  | 59  | 53  | 49  | 58  | 53  | 49  |  | 57  | 52  | 49  |  | 57  | 52  | 49  | 47  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 23883 |
| 5°  | 23284 |
| 10° | 22664 |
| 15° | 22242 |
| 20° | 21661 |
| 25° | 20894 |
| 30° | 19171 |
| 35° | 14700 |
| 40° | 6992  |
| 45° | 2665  |
| 50° | 1300  |
| 55° | 532   |
| 60° | 136   |
| 65° | 29    |
| 70° | 0     |
| 75° | 0     |
| 80° | 0     |
| 85° | 0     |



TEST NUMBER: P246289

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBW0B

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 70.9   | 8.4       |
| 10°-20°   | 196.1  | 23.1      |
| 20°-30°   | 279.9  | 33.1      |
| 30°-40°   | 232.0  | 27.4      |
| 40°-50°   | 57.2   | 6.8       |
| 50°-60°   | 10.3   | 1.2       |
| 60°-70°   | 0.6    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 546.9  | 64.6      |
| 0°-40°    | 778.9  | 92.0      |
| 0°-60°    | 846.4  | 99.9      |
| 0°-90°    | 847.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 847.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 774 |      |
| 5°  | 752 | 71   |
| 15° | 697 | 196  |
| 25° | 614 | 280  |
| 35° | 390 | 232  |
| 45° | 61  | 57   |
| 55° | 10  | 10   |
| 65° | 0   | 1    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P246289

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBW0B

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 774.5 |
| 2.5°  | 768.1 |
| 5°    | 752.2 |
| 7.5°  | 736.7 |
| 10°   | 723.8 |
| 12.5° | 711.3 |
| 15°   | 696.7 |
| 17.5° | 679.5 |
| 20°   | 660.1 |
| 22.5° | 638.2 |
| 25°   | 614.1 |
| 27.5° | 581.4 |
| 30°   | 538.4 |
| 32.5° | 477.8 |
| 35°   | 390.5 |
| 37.5° | 282.1 |
| 40°   | 173.7 |
| 42.5° | 101.1 |
| 45°   | 61.1  |
| 47.5° | 40.4  |
| 50°   | 27.1  |
| 52.5° | 17.6  |
| 55°   | 9.9   |
| 57.5° | 4.7   |
| 60°   | 2.2   |
| 62.5° | 0.9   |
| 65°   | 0.4   |
| 67.5° | 0.0   |
| 70°   | 0.0   |
| 72.5° | 0.0   |
| 75°   | 0.0   |
| 77.5° | 0.0   |
| 80°   | 0.0   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |

(END OF REPORT)