

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251406

Luminaire Tested: **LSR8B60D010 EC8B609730 8LBS0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B609730 8LBS0B
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4696.0 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251406

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBS0B

Luminous Intensity Polar Plot





TEST NUMBER: P251406

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBS0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	94	90	103	98	93	89	94	90	87		91	88	85		88	86	84	82
3	98	90	84	79	96	89	83	79	86	81	77		84	80	76		81	78	75	73
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75	71	67	66
5	86	75	68	63	84	74	68	63	72	66	62		71	65	61		69	64	61	59
6	80	69	62	56	78	68	61	56	67	60	56		65	60	55		64	59	55	53
7	75	63	56	51	73	63	56	51	61	55	51		60	54	50		59	54	50	48
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		54	49	46	44
9	66	54	47	42	65	54	47	42	53	46	42		52	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83887
5°	83796
10°	83356
15°	82750
20°	81835
25°	80542
30°	78178
35°	74502
40°	69003
45°	57900
50°	38282
55°	18897
60°	7499
65°	2919
70°	451
75°	0
80°	0
85°	0



TEST NUMBER: P251406

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBS0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.9	5.5
10°-20°	730.7	15.6
20°-30°	1087.6	23.2
30°-40°	1231.8	26.2
40°-50°	995.8	21.2
50°-60°	345.4	7.4
60°-70°	47.2	1.0
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2075.1	44.2
0°-40°	3306.9	70.4
0°-60°	4648.1	99.0
0°-90°	4696.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4696.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2720	
5°	2707	257
15°	2592	731
25°	2367	1088
35°	1979	1232
45°	1328	996
55°	352	345
65°	40	47
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P251406

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBS0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2720.4
2.5°	2717.0
5°	2707.1
7.5°	2687.1
10°	2662.1
12.5°	2628.8
15°	2592.1
17.5°	2545.5
20°	2493.8
22.5°	2433.9
25°	2367.2
27.5°	2287.3
30°	2195.6
32.5°	2092.3
35°	1979.1
37.5°	1854.1
40°	1714.2
42.5°	1542.6
45°	1327.7
47.5°	1067.8
50°	798.0
52.5°	546.4
55°	351.5
57.5°	208.2
60°	121.6
62.5°	71.6
65°	40.0
67.5°	18.3
70°	5.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)