

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251102

Luminaire Tested: **LSR8B60D010 EC8B609730 8LBS0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251102
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B609730 8LBS0WMH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4939.0 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251102

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBS0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P251102

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBS0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P251102

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBS0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	263.6	5.3
10°-20°	746.2	15.1
20°-30°	1110.9	22.5
30°-40°	1262.0	25.6
40°-50°	1031.5	20.9
50°-60°	404.2	8.2
60°-70°	94.2	1.9
70°-80°	22.7	0.5
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2120.7	42.9
0°-40°	3382.7	68.5
0°-60°	4818.4	97.6
0°-90°	4939.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4939.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2800	
5°	2781	264
15°	2646	746
25°	2417	1111
35°	2028	1262
45°	1370	1032
55°	420	404
65°	88	94
75°	21	23
85°	3	4
90°	0	



TEST NUMBER: P251102

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBS0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2800.3
2.5°	2795.9
5°	2781.0
7.5°	2755.8
10°	2724.6
12.5°	2685.9
15°	2645.8
17.5°	2598.3
20°	2546.3
22.5°	2485.4
25°	2417.1
27.5°	2336.8
30°	2246.2
32.5°	2143.7
35°	2027.8
37.5°	1900.1
40°	1757.5
42.5°	1585.1
45°	1369.7
47.5°	1117.2
50°	854.2
52.5°	613.5
55°	420.4
57.5°	274.8
60°	184.2
62.5°	126.3
65°	87.6
67.5°	57.9
70°	38.6
72.5°	26.7
75°	20.8
77.5°	14.9
80°	8.9
82.5°	4.5
85°	3.0
87.5°	1.5
90°	0.0

(END OF REPORT)