

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243991

Luminaire Tested: **LSR8B15D010 EC8B15940 8LBM0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243991
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15940 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 4000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1418.0 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243991

CATALOG NUMBER: LSR8B15D010 EC8B15940 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243991

CATALOG NUMBER: LSR8B15D010 EC8B15940 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72	79	75	72	77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68	75	71	68	74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64	71	67	64	70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58	65	61	58	64	60	58	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76280
5°	72999
10°	64988
15°	52209
20°	40891
25°	33017
30°	25583
35°	14572
40°	5495
45°	2372
50°	955
55°	355
60°	191
65°	131
70°	81
75°	48
80°	0
85°	0



TEST NUMBER: P243991

CATALOG NUMBER: LSR8B15D010 EC8B15940 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.5	15.3
10°-20°	454.1	32.0
20°-30°	444.4	31.3
30°-40°	245.9	17.3
40°-50°	47.6	3.4
50°-60°	7.3	0.5
60°-70°	1.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	1115.0	78.6
0°-40°	1360.9	96.0
0°-60°	1415.7	99.8
0°-90°	1418.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1418.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2474	
5°	2358	216
15°	1635	454
25°	970	444
35°	387	246
45°	54	48
55°	7	7
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P243991

CATALOG NUMBER: LSR8B15D010 EC8B15940 8LBM0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2473.7
2.5°	2439.7
5°	2358.3
7.5°	2244.3
10°	2075.5
12.5°	1862.1
15°	1635.4
17.5°	1422.9
20°	1246.1
22.5°	1099.9
25°	970.4
27.5°	848.4
30°	718.5
32.5°	566.1
35°	387.1
37.5°	232.9
40°	136.5
42.5°	85.3
45°	54.4
47.5°	34.0
50°	19.9
52.5°	11.0
55°	6.6
57.5°	4.0
60°	3.1
62.5°	2.2
65°	1.8
67.5°	1.3
70°	0.9
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)