

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251441

Luminaire Tested: **LSR8B70D010 EC8B70830 8LBN0MW**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251441  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B70D010 EC8B70830 8LBN0MW  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 3000 CCT WITH MATTE WHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6667.0 lumens  
Efficiency: N/A  
Efficacy: 87.8 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 75.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251441

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBN0MW

### Luminous Intensity Polar Plot





TEST NUMBER: P251441

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBN0MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71		78	74	70		76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55		64	59	55		63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	215595
5°	214051
10°	195058
15°	167193
20°	148174
25°	132224
30°	106785
35°	74091
40°	47009
45°	34922
50°	29805
55°	26128
60°	23386
65°	20890
70°	18005
75°	16561
80°	15432
85°	13622



TEST NUMBER: P251441

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBN0MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	637.8	9.6
10°-20°	1475.2	22.1
20°-30°	1754.4	26.3
30°-40°	1240.2	18.6
40°-50°	640.2	9.6
50°-60°	438.9	6.6
60°-70°	284.9	4.3
70°-80°	149.4	2.2
80°-90°	45.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3867.5	58.0
0°-40°	5107.7	76.6
0°-60°	6186.8	92.8
0°-90°	6667.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6667.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6992	
5°	6915	638
15°	5237	1475
25°	3886	1754
35°	1968	1240
45°	801	640
55°	486	439
65°	286	285
75°	139	149
85°	38	43
90°	0	3
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251441

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBN0MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6991.6
2.5°	6991.6
5°	6915.1
7.5°	6660.8
10°	6229.5
12.5°	5715.1
15°	5237.2
17.5°	4844.0
20°	4515.4
22.5°	4204.6
25°	3886.2
27.5°	3486.6
30°	2999.0
32.5°	2474.4
35°	1968.2
37.5°	1516.4
40°	1167.8
42.5°	939.8
45°	800.8
47.5°	699.8
50°	621.3
52.5°	552.5
55°	486.0
57.5°	427.5
60°	379.2
62.5°	328.6
65°	286.3
67.5°	248.1
70°	199.7
72.5°	171.5
75°	139.0
77.5°	112.8
80°	86.9
82.5°	64.7
85°	38.5
87.5°	22.2
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251441

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBN0MW

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)