

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250474

Luminaire Tested: **LSR8B150D010 EC8B150835 8LBM0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250474
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14005)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B150D010 EC8B150835 8LBM0GPH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14073.0 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 158.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250474

CATALOG NUMBER: LSR8B150D010 EC8B150835 8LBM0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250474

CATALOG NUMBER: LSR8B150D010 EC8B150835 8LBM0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	550376
5°	536459
10°	480909
15°	428316
20°	390732
25°	355004
30°	291099
35°	191575
40°	95567
45°	35568
50°	10803
55°	1306
60°	752
65°	0
70°	550
75°	2180
80°	0
85°	2158



TEST NUMBER: P250474

CATALOG NUMBER: LSR8B150D010 EC8B150835 8LBM0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1589.0	11.3
10°-20°	3778.0	26.8
20°-30°	4706.8	33.4
30°-40°	3174.9	22.6
40°-50°	750.7	5.3
50°-60°	54.9	0.4
60°-70°	9.8	0.1
70°-80°	7.2	0.1
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10073.9	71.6
0°-40°	13248.7	94.1
0°-60°	14054.3	99.9
0°-90°	14073.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	14073.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17848	
5°	17331	###
15°	13417	3778
25°	10434	4707
35°	5089	3175
45°	816	751
55°	24	55
65°	0	10
75°	18	7
85°	6	2
90°	0	



TEST NUMBER: P250474

CATALOG NUMBER: LSR8B150D010 EC8B150835 8LBM0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	17848.3
2.5°	17817.9
5°	17330.8
7.5°	16448.1
10°	15358.6
12.5°	14329.8
15°	13416.7
17.5°	12631.3
20°	11907.0
22.5°	11213.0
25°	10433.9
27.5°	9417.3
30°	8175.4
32.5°	6671.9
35°	5089.1
37.5°	3640.3
40°	2374.1
42.5°	1418.4
45°	815.6
47.5°	456.5
50°	225.2
52.5°	103.5
55°	24.3
57.5°	6.1
60°	12.2
62.5°	18.3
65°	0.0
67.5°	12.2
70°	6.1
72.5°	6.1
75°	18.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	6.1
87.5°	0.0
90°	0.0

(END OF REPORT)