

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251011

Luminaire Tested: **LSR8B70D010 EC8B70830 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251011
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B70D010 EC8B70830 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7042.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251011

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P251011

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	157370
5°	154204
10°	149321
15°	147307
20°	146429
25°	144579
30°	136808
35°	112835
40°	70456
45°	45306
50°	35135
55°	27047
60°	20494
65°	13316
70°	5698
75°	2788
80°	1243
85°	814



TEST NUMBER: P251011

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	468.6	6.7
10°-20°	1303.6	18.5
20°-30°	1941.7	27.6
30°-40°	1803.3	25.6
40°-50°	851.7	12.1
50°-60°	457.6	6.5
60°-70°	183.7	2.6
70°-80°	28.9	0.4
80°-90°	2.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3713.9	52.7
0°-40°	5517.2	78.3
0°-60°	6826.5	96.9
0°-90°	7042.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7042.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5103	
5°	4982	469
15°	4614	1304
25°	4249	1942
35°	2997	1803
45°	1039	852
55°	503	458
65°	182	184
75°	23	29
85°	2	3
90°	0	



TEST NUMBER: P251011

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5103.4
2.5°	5068.3
5°	4981.7
7.5°	4871.7
10°	4768.8
12.5°	4684.5
15°	4614.3
17.5°	4541.8
20°	4462.2
22.5°	4371.0
25°	4249.3
27.5°	4078.5
30°	3842.2
32.5°	3495.9
35°	2997.4
37.5°	2361.0
40°	1750.3
42.5°	1303.3
45°	1038.9
47.5°	868.1
50°	732.4
52.5°	610.7
55°	503.1
57.5°	409.5
60°	332.3
62.5°	259.7
65°	182.5
67.5°	107.6
70°	63.2
72.5°	37.4
75°	23.4
77.5°	14.0
80°	7.0
82.5°	4.7
85°	2.3
87.5°	0.0
90°	0.0

(END OF REPORT)