

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250941

Luminaire Tested: **LSR8B70D010 EC8B70835 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250941
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B70D010 EC8B70835 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6819.0 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250941

CATALOG NUMBER: LSR8B70D010 EC8B70835 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P250941

CATALOG NUMBER: LSR8B70D010 EC8B70835 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		64	60	57	56
10	74	64	59	55	73	64	58	55	63	58	55		62	58	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	320984
5°	299397
10°	258080
15°	223351
20°	194293
25°	166977
30°	131200
35°	76549
40°	35319
45°	18277
50°	9168
55°	4457
60°	2270
65°	1343
70°	622
75°	548
80°	408
85°	0



TEST NUMBER: P250941

CATALOG NUMBER: LSR8B70D010 EC8B70835 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	875.3	12.8
10°-20°	1956.2	28.7
20°-30°	2224.1	32.6
30°-40°	1306.2	19.2
40°-50°	350.5	5.1
50°-60°	83.2	1.2
60°-70°	18.9	0.3
70°-80°	4.2	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5055.6	74.1
0°-40°	6361.8	93.3
0°-60°	6795.5	99.7
0°-90°	6819.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6819.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10409	
5°	9672	875
15°	6996	1956
25°	4908	2224
35°	2034	1306
45°	419	351
55°	83	83
65°	18	19
75°	5	4
85°	0	0
90°	0	



TEST NUMBER: P250941

CATALOG NUMBER: LSR8B70D010 EC8B70835 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	10409.3
1°	10351.7
2°	10245.8
3°	10096.1
4°	9902.6
5°	9672.3
6°	9412.1
7°	9117.3
8°	8822.5
9°	8525.5
10°	8242.2
11°	7965.9
12°	7705.6
13°	7463.8
14°	7222.0
15°	6996.3
16°	6775.2
17°	6556.5
18°	6344.6
19°	6130.4
20°	5920.8
21°	5711.3
22°	5510.9
23°	5312.9
24°	5110.2
25°	4907.6
26°	4698.0
27°	4470.0
28°	4230.5
29°	3968.0
30°	3684.7
32.5°	2890.2
35°	2033.5
37.5°	1340.3
40°	877.4
42.5°	605.7
45°	419.1
47.5°	287.9
50°	191.1
52.5°	124.4
55°	82.9
57.5°	55.3
60°	36.8
62.5°	25.3
65°	18.4



TEST NUMBER: P250941

CATALOG NUMBER: LSR8B70D010 EC8B70835 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	11.5
70°	6.9
72.5°	4.6
75°	4.6
77.5°	2.3
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)