

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247850

Luminaire Tested: **LSR8B150D010 EC8B150850 8LBM0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247850
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-90)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B150D010 EC8B150850 8LBMOLI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16814.0 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 158.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247850

CATALOG NUMBER: LSR8B150D010 EC8B150850 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247850

CATALOG NUMBER: LSR8B150D010 EC8B150850 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88
3	103	97	93	89	102	96	92	88	93	90	87	91	88	85	89	86	84	83
4	99	91	86	82	97	90	86	82	88	84	81	86	83	80	84	81	79	78
5	94	86	81	77	92	85	80	76	83	79	76	82	78	75	80	77	74	73
6	90	81	76	72	88	80	75	71	79	74	71	78	73	70	76	73	70	68
7	86	77	71	67	84	76	71	67	75	70	67	74	69	66	73	69	66	65
8	82	73	67	63	80	72	67	63	71	66	63	70	66	62	69	65	62	61
9	78	69	63	60	77	68	63	59	68	63	59	67	62	59	66	62	59	58
10	75	66	60	56	74	65	60	56	64	59	56	64	59	56	63	59	56	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	810101
5°	786860
10°	696373
15°	591895
20°	492817
25°	398555
30°	296205
35°	184886
40°	91046
45°	38516
50°	13946
55°	4301
60°	2313
65°	963
70°	1001
75°	238
80°	355
85°	0



TEST NUMBER: P247850

CATALOG NUMBER: LSR8B150D010 EC8B150850 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2324.9	13.8
10°-20°	5157.1	30.7
20°-30°	5327.3	31.7
30°-40°	3105.7	18.5
40°-50°	778.3	4.6
50°-60°	94.3	0.6
60°-70°	19.7	0.1
70°-80°	2.5	0.0
80°-90°	4.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	12809.3	76.2
0°-40°	15915.0	94.7
0°-60°	16787.6	99.8
0°-90°	16814.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	16814.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	26271	
5°	25420	###
15°	18541	5157
25°	11714	5327
35°	4911	3106
45°	883	778
55°	80	94
65°	13	20
75°	2	3
85°	0	4
90°	0	



TEST NUMBER: P247850

CATALOG NUMBER: LSR8B150D010 EC8B150850 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	26271.0
2.5°	26067.4
5°	25420.2
7.5°	24146.0
10°	22239.8
12.5°	20351.8
15°	18540.7
17.5°	16723.6
20°	15017.9
22.5°	13379.1
25°	11713.9
27.5°	10057.9
30°	8318.8
32.5°	6603.0
35°	4911.4
37.5°	3450.9
40°	2261.8
42.5°	1425.1
45°	883.2
47.5°	538.9
50°	290.7
52.5°	141.8
55°	80.0
57.5°	43.6
60°	37.5
62.5°	26.3
65°	13.2
67.5°	16.2
70°	11.1
72.5°	0.0
75°	2.0
77.5°	1.0
80°	2.0
82.5°	3.0
85°	0.0
87.5°	11.1
90°	0.0

(END OF REPORT)