

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250847

Luminaire Tested: **LSR8B70D010 EC8B70840 8LBM0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250847
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B70D010 EC8B70840 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7759.0 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250847

CATALOG NUMBER: LSR8B70D010 EC8B70840 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P250847

CATALOG NUMBER: LSR8B70D010 EC8B70840 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72		79	75	72		77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68		75	71	68		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58		65	61	58		64	60	58	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	417385
5°	399444
10°	355607
15°	285679
20°	223751
25°	180658
30°	139988
35°	79734
40°	30074
45°	12969
50°	5219
55°	1952
60°	1042
65°	708
70°	433
75°	286
80°	0
85°	0



TEST NUMBER: P250847

CATALOG NUMBER: LSR8B70D010 EC8B70840 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1184.4	15.3
10°-20°	2484.9	32.0
20°-30°	2431.6	31.3
30°-40°	1345.3	17.3
40°-50°	260.4	3.4
50°-60°	39.9	0.5
60°-70°	9.8	0.1
70°-80°	2.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6101.0	78.6
0°-40°	7446.3	96.0
0°-60°	7746.6	99.8
0°-90°	7759.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7759.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13536	
5°	12904	###
15°	8949	2485
25°	5310	2432
35°	2118	1345
45°	297	260
55°	36	40
65°	10	10
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P250847

CATALOG NUMBER: LSR8B70D010 EC8B70840 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	13535.5
2.5°	13349.3
5°	12904.4
7.5°	12280.6
10°	11356.9
12.5°	10189.1
15°	8948.7
17.5°	7785.7
20°	6818.5
22.5°	6018.2
25°	5309.7
27.5°	4642.4
30°	3931.5
32.5°	3097.3
35°	2118.1
37.5°	1274.2
40°	747.1
42.5°	466.7
45°	297.4
47.5°	186.2
50°	108.8
52.5°	60.4
55°	36.3
57.5°	21.8
60°	16.9
62.5°	12.1
65°	9.7
67.5°	7.3
70°	4.8
72.5°	2.4
75°	2.4
77.5°	2.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)