

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250825

Luminaire Tested: **LSR8B70D010 EC8B70850 8LBN0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250825
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B70D010 EC8B70850 8LBNOLI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7270.0 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250825

CATALOG NUMBER: LSR8B70D010 EC8B70850 8LBNOLI

Luminous Intensity Polar Plot





TEST NUMBER: P250825

CATALOG NUMBER: LSR8B70D010 EC8B70850 8LBNOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78		83	80	77		82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71		77	74	71		76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68		75	71	68		74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66		72	68	66		71	68	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1098334
5°	762848
10°	401429
15°	253988
20°	188750
25°	148393
30°	106834
35°	45847
40°	15977
45°	6127
50°	1420
55°	532
60°	0
65°	722
70°	225
75°	584
80°	870
85°	0



TEST NUMBER: P250825

CATALOG NUMBER: LSR8B70D010 EC8B70850 8LBNOLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1975.8	27.2
10°-20°	2295.6	31.6
20°-30°	1981.3	27.3
30°-40°	859.5	11.8
40°-50°	134.7	1.9
50°-60°	9.7	0.1
60°-70°	5.3	0.1
70°-80°	5.5	0.1
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6252.6	86.0
0°-40°	7112.1	97.8
0°-60°	7256.6	99.8
0°-90°	7270.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7270.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	35618	
5°	24644	###
15°	7956	2296
25°	4361	1981
35°	1218	860
45°	140	135
55°	10	10
65°	10	5
75°	5	5
85°	0	3
90°	0	



TEST NUMBER: P250825

CATALOG NUMBER: LSR8B70D010 EC8B70850 8LBNOLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	35618.2
2.5°	32164.1
5°	24644.5
7.5°	17576.1
10°	12820.3
12.5°	9837.1
15°	7956.0
17.5°	6691.2
20°	5751.9
22.5°	4950.6
25°	4361.4
27.5°	3740.1
30°	3000.4
32.5°	2085.8
35°	1217.9
37.5°	680.5
40°	396.9
42.5°	246.5
45°	140.5
47.5°	113.4
50°	29.6
52.5°	14.8
55°	9.9
57.5°	4.9
60°	0.0
62.5°	2.5
65°	9.9
67.5°	7.4
70°	2.5
72.5°	12.3
75°	4.9
77.5°	0.0
80°	4.9
82.5°	2.5
85°	0.0
87.5°	4.9
90°	0.0

(END OF REPORT)