

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250600

Luminaire Tested: **LSR8B150D010 EC8B150940 8LBM0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250600
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13928)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B150D010 EC8B150940 8LBM0B
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 4000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9107.0 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 158.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250600

CATALOG NUMBER: LSR8B150D010 EC8B150940 8LBM0B

Luminous Intensity Polar Plot





TEST NUMBER: P250600

CATALOG NUMBER: LSR8B150D010 EC8B150940 8LBM0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	364380
5°	353239
10°	309369
15°	273127
20°	250279
25°	230449
30°	191806
35°	127399
40°	62003
45°	22454
50°	6759
55°	473
60°	0
65°	321
70°	0
75°	0
80°	781
85°	0



TEST NUMBER: P250600

CATALOG NUMBER: LSR8B150D010 EC8B150940 8LBM0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1037.9	11.4
10°-20°	2410.4	26.5
20°-30°	3057.9	33.6
30°-40°	2094.9	23.0
40°-50°	477.4	5.2
50°-60°	23.8	0.3
60°-70°	1.1	0.0
70°-80°	1.7	0.0
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6506.2	71.4
0°-40°	8601.1	94.4
0°-60°	9102.3	99.9
0°-90°	9107.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9107.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11817	
5°	11412	###
15°	8556	2410
25°	6773	3058
35°	3384	2095
45°	515	477
55°	9	24
65°	4	1
75°	0	2
85°	0	2
90°	0	



TEST NUMBER: P250600

CATALOG NUMBER: LSR8B150D010 EC8B150940 8LBM0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	11816.6
1°	11878.2
2°	11856.2
3°	11768.2
4°	11618.5
5°	11411.7
6°	11160.8
7°	10870.4
8°	10549.1
9°	10205.8
10°	9880.2
11°	9580.9
12°	9259.7
13°	9026.4
14°	8779.9
15°	8555.5
16°	8353.1
17°	8154.9
18°	7970.2
19°	7789.7
20°	7626.9
21°	7459.6
22°	7288.0
23°	7138.4
24°	6971.2
25°	6773.1
26°	6553.0
27°	6297.8
28°	6024.9
29°	5721.3
30°	5386.8
31°	5008.3
32°	4616.6
33°	4207.3
34°	3789.2
35°	3384.3
37.5°	2389.7
40°	1540.3
42.5°	906.6
45°	514.9
47.5°	277.3
50°	140.9
52.5°	26.4
55°	8.8
57.5°	4.4



TEST NUMBER: P250600

CATALOG NUMBER: LSR8B150D010 EC8B150940 8LBM0B

CANDELA DISTRIBUTION (continued):

	0°
60°	0.0
62.5°	0.0
65°	4.4
67.5°	0.0
70°	0.0
72.5°	4.4
75°	0.0
77.5°	0.0
80°	4.4
82.5°	0.0
85°	0.0
87.5°	4.4
90°	0.0

(END OF REPORT)