

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251275

Luminaire Tested: **LSR8B70D010 EC8B70930 8LBM0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251275
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201629)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B70D010 EC8B70930 8LBM0GPH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6138.7 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251275

CATALOG NUMBER: LSR8B70D010 EC8B70930 8LBM0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P251275

CATALOG NUMBER: LSR8B70D010 EC8B70930 8LBM0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	240110
5°	234016
10°	209831
15°	186842
20°	170485
25°	154823
30°	126970
35°	83604
40°	41663
45°	15490
50°	4716
55°	532
60°	327
65°	0
70°	225
75°	917
80°	0
85°	885



TEST NUMBER: P251275

CATALOG NUMBER: LSR8B70D010 EC8B70930 8LBM0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	693.2	11.3
10°-20°	1648.1	26.8
20°-30°	2053.0	33.4
30°-40°	1385.3	22.6
40°-50°	327.4	5.3
50°-60°	23.8	0.4
60°-70°	4.2	0.1
70°-80°	3.0	0.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4394.3	71.6
0°-40°	5779.6	94.2
0°-60°	6130.8	99.9
0°-90°	6138.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6138.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7787	
5°	7560	693
15°	5853	1648
25°	4550	2053
35°	2221	1385
45°	355	327
55°	10	24
65°	0	4
75°	8	3
85°	2	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251275

CATALOG NUMBER: LSR8B70D010 EC8B70930 8LBM0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	7786.6
2.5°	7774.2
5°	7560.1
7.5°	7174.6
10°	6701.3
12.5°	6250.6
15°	5852.7
17.5°	5509.9
20°	5195.3
22.5°	4890.6
25°	4550.4
27.5°	4107.3
30°	3565.9
32.5°	2911.1
35°	2220.9
37.5°	1589.2
40°	1035.0
42.5°	619.4
45°	355.2
47.5°	199.1
50°	98.3
52.5°	45.3
55°	9.9
57.5°	2.5
60°	5.3
62.5°	7.7
65°	0.0
67.5°	5.3
70°	2.5
72.5°	2.5
75°	7.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	2.5
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251275

CATALOG NUMBER: LSR8B70D010 EC8B70930 8LBM0GPH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)