

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251187

Luminaire Tested: **LSR8B70D010 EC8B70930 8LBS0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251187  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B70D010 EC8B70930 8LBS0WH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 3000 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7788.7 lumens  
Efficiency: N/A  
Efficacy: 102.6 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 75.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251187

CATALOG NUMBER: LSR8B70D010 EC8B70930 8LBS0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P251187

CATALOG NUMBER: LSR8B70D010 EC8B70930 8LBS0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	136037
5°	136557
10°	138280
15°	140983
20°	142996
25°	143582
30°	139183
35°	127038
40°	109893
45°	86507
50°	55807
55°	27391
60°	11261
65°	4932
70°	1425
75°	536
80°	391
85°	0



TEST NUMBER: P251187

CATALOG NUMBER: LSR8B70D010 EC8B70930 8LBS0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	421.3	5.4
10°-20°	1248.0	16.0
20°-30°	1932.3	24.8
30°-40°	2093.3	26.9
40°-50°	1506.3	19.3
50°-60°	504.0	6.5
60°-70°	76.2	1.0
70°-80°	6.5	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3601.6	46.2
0°-40°	5694.9	73.1
0°-60°	7705.2	98.9
0°-90°	7788.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7788.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4412	
5°	4412	421
15°	4416	1248
25°	4220	1932
35°	3375	2093
45°	1984	1506
55°	510	504
65°	68	76
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P251187

CATALOG NUMBER: LSR8B70D010 EC8B70930 8LBS0WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4411.6
2.5°	4411.6
5°	4411.6
7.5°	4413.8
10°	4416.2
12.5°	4420.7
15°	4416.2
17.5°	4398.1
20°	4357.6
22.5°	4296.7
25°	4220.0
27.5°	4098.3
30°	3908.9
32.5°	3661.0
35°	3374.7
37.5°	3065.8
40°	2730.0
42.5°	2369.2
45°	1983.7
47.5°	1566.7
50°	1163.3
52.5°	798.0
55°	509.5
57.5°	304.4
60°	182.6
62.5°	110.4
65°	67.6
67.5°	33.9
70°	15.8
72.5°	6.7
75°	4.5
77.5°	4.5
80°	2.2
82.5°	2.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)