

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P248015

Luminaire Tested: **LSR8B150D010 EC8B1509730 8LBW0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P248015  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-71)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B150D010 EC8B1509730 8LBW0WMH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 3000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11674.0 lumens  
Efficiency: N/A  
Efficacy: 73.7 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 158.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P248015

CATALOG NUMBER: LSR8B150D010 EC8B1509730 8LBW0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P248015

CATALOG NUMBER: LSR8B150D010 EC8B1509730 8LBW0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47
9	68	57	50	46	67	56	50	46	55	49	45	54	49	45	54	49	45	43
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P248015

CATALOG NUMBER: LSR8B150D010 EC8B1509730 8LBW0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	771.9	6.6
10°-20°	2173.9	18.6
20°-30°	3174.6	27.2
30°-40°	2855.1	24.5
40°-50°	1561.4	13.4
50°-60°	774.1	6.6
60°-70°	305.7	2.6
70°-80°	49.3	0.4
80°-90°	8.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6120.4	52.4
0°-40°	8975.5	76.9
0°-60°	11311.0	96.9
0°-90°	11674.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11674.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8238	
5°	8151	772
15°	7702	2174
25°	7006	3175
35°	4608	2855
45°	1944	1561
55°	840	774
65°	306	306
75°	38	49
85°	10	8
90°	0	



TEST NUMBER: P248015

CATALOG NUMBER: LSR8B150D010 EC8B1509730 8LBW0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8237.7
2.5°	8214.8
5°	8150.8
7.5°	8067.5
10°	7950.4
12.5°	7825.9
15°	7702.1
17.5°	7569.5
20°	7419.2
22.5°	7247.6
25°	7005.9
27.5°	6599.3
30°	6056.3
32.5°	5372.0
35°	4608.0
37.5°	3845.5
40°	3116.9
42.5°	2460.5
45°	1944.1
47.5°	1558.1
50°	1286.3
52.5°	1046.8
55°	839.8
57.5°	678.5
60°	542.9
62.5°	429.5
65°	305.7
67.5°	182.0
70°	109.8
72.5°	61.9
75°	37.6
77.5°	24.3
80°	17.7
82.5°	5.9
85°	10.3
87.5°	4.4
90°	0.0

(END OF REPORT)