

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245672

Luminaire Tested: **LSR8B20D010 EC8B20827 8LBM0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245672  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201629)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B20D010 EC8B20827 8LBM0GPH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 2700 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1796.0 lumens  
Efficiency: N/A  
Efficacy: 84.3 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245672

CATALOG NUMBER: LSR8B20D010 EC8B20827 8LBM0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245672

CATALOG NUMBER: LSR8B20D010 EC8B20827 8LBM0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	70251
5°	68467
10°	61393
15°	54667
20°	49879
25°	45296
30°	37148
35°	24461
40°	12189
45°	4531
50°	1382
55°	156
60°	93
65°	0
70°	63
75°	262
80°	0
85°	248



TEST NUMBER: P245672

CATALOG NUMBER: LSR8B20D010 EC8B20827 8LBM0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	202.8	11.3
10°-20°	482.2	26.8
20°-30°	600.6	33.4
30°-40°	405.3	22.6
40°-50°	95.8	5.3
50°-60°	7.0	0.4
60°-70°	1.2	0.1
70°-80°	0.9	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1285.7	71.6
0°-40°	1691.0	94.2
0°-60°	1793.7	99.9
0°-90°	1796.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1796.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2278	
5°	2212	203
15°	1712	482
25°	1331	601
35°	650	405
45°	104	96
55°	3	7
65°	0	1
75°	2	1
85°	1	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245672

CATALOG NUMBER: LSR8B20D010 EC8B20827 8LBM0GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2278.2
2.5°	2274.6
5°	2211.9
7.5°	2099.1
10°	1960.7
12.5°	1828.8
15°	1712.4
17.5°	1612.1
20°	1520.0
22.5°	1430.9
25°	1331.3
27.5°	1201.7
30°	1043.3
32.5°	851.7
35°	649.8
37.5°	465.0
40°	302.8
42.5°	181.2
45°	103.9
47.5°	58.2
50°	28.8
52.5°	13.3
55°	2.9
57.5°	0.7
60°	1.5
62.5°	2.2
65°	0.0
67.5°	1.5
70°	0.7
72.5°	0.7
75°	2.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.7
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245672

CATALOG NUMBER: LSR8B20D010 EC8B20827 8LBM0GPH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)