

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244016

Luminaire Tested: **LSR8B20D010 EC8B20827 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244016
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B20D010 EC8B20827 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 2700 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2300.0 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244016

CATALOG NUMBER: LSR8B20D010 EC8B20827 8LBS0LI

Luminous Intensity Polar Plot





TEST NUMBER: P244016

CATALOG NUMBER: LSR8B20D010 EC8B20827 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88		91	88	86		88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78		84	80	77		82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63		71	66	62		69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56		66	60	56		64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51		61	55	51		59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47		56	51	46		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39		49	43	39		48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39544
5°	39714
10°	40361
15°	41380
20°	42102
25°	42149
30°	40844
35°	37396
40°	32501
45°	25716
50°	16675
55°	8333
60°	3497
65°	1540
70°	478
75°	238
80°	231
85°	248



TEST NUMBER: P244016

CATALOG NUMBER: LSR8B20D010 EC8B20827 8LBS0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	5.3
10°-20°	366.3	15.9
20°-30°	567.4	24.7
30°-40°	616.2	26.8
40°-50°	447.8	19.5
50°-60°	152.2	6.6
60°-70°	24.3	1.1
70°-80°	2.6	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1056.4	45.9
0°-40°	1672.6	72.7
0°-60°	2272.5	98.8
0°-90°	2300.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2300.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1282	
5°	1283	123
15°	1296	366
25°	1239	567
35°	993	616
45°	590	448
55°	155	152
65°	21	24
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P244016

CATALOG NUMBER: LSR8B20D010 EC8B20827 8LBSOLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1282.4
2.5°	1282.4
5°	1283.0
7.5°	1285.0
10°	1289.0
12.5°	1293.6
15°	1296.2
17.5°	1293.6
20°	1283.0
22.5°	1263.9
25°	1238.8
27.5°	1201.2
30°	1147.1
32.5°	1075.2
35°	993.4
37.5°	904.4
40°	807.4
42.5°	702.5
45°	589.7
47.5°	468.4
50°	347.6
52.5°	238.1
55°	155.0
57.5°	94.3
60°	56.7
62.5°	35.0
65°	21.1
67.5°	11.9
70°	5.3
72.5°	3.3
75°	2.0
77.5°	1.3
80°	1.3
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)