

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245570

Luminaire Tested: **LSR8B20D010 EC8B20935 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245570
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B20D010 EC8B20935 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3500 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1669.0 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245570

CATALOG NUMBER: LSR8B20D010 EC8B20935 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245570

CATALOG NUMBER: LSR8B20D010 EC8B20935 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 113 | 110 | 107 | 104 | 110 | 108 | 105 | 103 | 103 | 101 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 |
| 2 | 106 | 101 | 96 | 92 | 104 | 99 | 95 | 91 | 96 | 92 | 89 | 93 | 90 | 87 | 90 | 88 | 86 | 84 |
| 3 | 100 | 93 | 87 | 83 | 98 | 91 | 86 | 82 | 89 | 84 | 81 | 86 | 82 | 79 | 84 | 81 | 78 | 76 |
| 4 | 94 | 85 | 79 | 74 | 92 | 84 | 78 | 74 | 82 | 77 | 73 | 80 | 76 | 72 | 78 | 74 | 71 | 70 |
| 5 | 88 | 79 | 72 | 67 | 87 | 78 | 72 | 67 | 76 | 71 | 66 | 74 | 70 | 66 | 73 | 69 | 65 | 64 |
| 6 | 83 | 73 | 66 | 61 | 82 | 72 | 66 | 61 | 71 | 65 | 61 | 69 | 64 | 60 | 68 | 63 | 60 | 58 |
| 7 | 78 | 68 | 61 | 56 | 77 | 67 | 61 | 56 | 66 | 60 | 56 | 65 | 59 | 56 | 63 | 59 | 55 | 54 |
| 8 | 74 | 63 | 56 | 52 | 73 | 63 | 56 | 52 | 61 | 56 | 51 | 60 | 55 | 51 | 59 | 55 | 51 | 49 |
| 9 | 70 | 59 | 52 | 48 | 69 | 58 | 52 | 48 | 57 | 52 | 48 | 57 | 51 | 47 | 56 | 51 | 47 | 46 |
| 10 | 66 | 55 | 49 | 44 | 65 | 55 | 49 | 44 | 54 | 48 | 44 | 53 | 48 | 44 | 52 | 47 | 44 | 43 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 40075 |
| 5° | 39126 |
| 10° | 37900 |
| 15° | 37351 |
| 20° | 36911 |
| 25° | 36120 |
| 30° | 33830 |
| 35° | 27623 |
| 40° | 16492 |
| 45° | 9904 |
| 50° | 7138 |
| 55° | 4860 |
| 60° | 3047 |
| 65° | 1496 |
| 70° | 379 |
| 75° | 143 |
| 80° | 107 |
| 85° | 0 |



TEST NUMBER: P245570

CATALOG NUMBER: LSR8B20D010 EC8B20935 8LBW0GPH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 118.9 | 7.1 |
| 10°-20° | 330.2 | 19.8 |
| 20°-30° | 484.9 | 29.1 |
| 30°-40° | 439.6 | 26.3 |
| 40°-50° | 188.2 | 11.3 |
| 50°-60° | 83.3 | 5.0 |
| 60°-70° | 22.2 | 1.3 |
| 70°-80° | 1.7 | 0.1 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 934.0 | 56.0 |
| 0°-40° | 1373.5 | 82.3 |
| 0°-60° | 1645.0 | 98.6 |
| 0°-90° | 1669.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1669.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1300 | |
| 5° | 1264 | 119 |
| 15° | 1170 | 330 |
| 25° | 1062 | 485 |
| 35° | 734 | 440 |
| 45° | 227 | 188 |
| 55° | 90 | 83 |
| 65° | 20 | 22 |
| 75° | 1 | 2 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P245570

CATALOG NUMBER: LSR8B20D010 EC8B20935 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1299.6 |
| 2.5° | 1289.3 |
| 5° | 1264.0 |
| 7.5° | 1235.1 |
| 10° | 1210.4 |
| 12.5° | 1189.9 |
| 15° | 1170.0 |
| 17.5° | 1148.9 |
| 20° | 1124.8 |
| 22.5° | 1096.5 |
| 25° | 1061.6 |
| 27.5° | 1014.6 |
| 30° | 950.1 |
| 32.5° | 859.8 |
| 35° | 733.8 |
| 37.5° | 568.7 |
| 40° | 409.7 |
| 42.5° | 295.8 |
| 45° | 227.1 |
| 47.5° | 183.2 |
| 50° | 148.8 |
| 52.5° | 118.1 |
| 55° | 90.4 |
| 57.5° | 67.5 |
| 60° | 49.4 |
| 62.5° | 34.3 |
| 65° | 20.5 |
| 67.5° | 9.0 |
| 70° | 4.2 |
| 72.5° | 2.4 |
| 75° | 1.2 |
| 77.5° | 0.6 |
| 80° | 0.6 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)