

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251051

Luminaire Tested: **LSR8B70D010 EC8B70950 8LBN0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251051  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B70D010 EC8B70950 8LBN0WMH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 5000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6102.0 lumens  
Efficiency: N/A  
Efficacy: 80.4 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 75.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251051

CATALOG NUMBER: LSR8B70D010 EC8B70950 8LBN0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P251051

CATALOG NUMBER: LSR8B70D010 EC8B70950 8LBN0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59	66	62	59	65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	274027
5°	270208
10°	247233
15°	212267
20°	178745
25°	147648
30°	110772
35°	66024
40°	31446
45°	13702
50°	6184
55°	2715
60°	1610
65°	883
70°	911
75°	0
80°	355
85°	1486



TEST NUMBER: P251051

CATALOG NUMBER: LSR8B70D010 EC8B70950 8LBN0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	806.1	13.2
10°-20°	1852.7	30.4
20°-30°	1965.8	32.2
30°-40°	1121.7	18.4
40°-50°	278.0	4.6
50°-60°	54.6	0.9
60°-70°	16.4	0.3
70°-80°	3.7	0.1
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4624.7	75.8
0°-40°	5746.3	94.2
0°-60°	6078.9	99.6
0°-90°	6102.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6102.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8886	
5°	8729	806
15°	6649	1853
25°	4340	1966
35°	1754	1122
45°	314	278
55°	50	55
65°	12	16
75°	0	4
85°	4	3
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251051

CATALOG NUMBER: LSR8B70D010 EC8B70950 8LBN0WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8886.5
2.5°	8882.4
5°	8729.3
7.5°	8392.9
10°	7895.8
12.5°	7295.5
15°	6649.1
17.5°	6033.0
20°	5447.0
22.5°	4883.4
25°	4339.5
27.5°	3755.5
30°	3111.0
32.5°	2418.3
35°	1753.9
37.5°	1208.3
40°	781.2
42.5°	495.3
45°	314.2
47.5°	205.5
50°	128.9
52.5°	78.4
55°	50.5
57.5°	40.4
60°	26.1
62.5°	24.2
65°	12.1
67.5°	12.1
70°	10.1
72.5°	5.9
75°	0.0
77.5°	2.0
80°	2.0
82.5°	4.2
85°	4.2
87.5°	2.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251051

CATALOG NUMBER: LSR8B70D010 EC8B70950 8LBN0WMH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)