

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244358

Luminaire Tested: **LSR8B20D010 EC8B20950 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244358
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B20D010 EC8B20950 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 5000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1855.0 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244358

CATALOG NUMBER: LSR8B20D010 EC8B20950 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P244358

CATALOG NUMBER: LSR8B20D010 EC8B20950 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		64	60	57	56
10	74	64	59	55	73	64	58	55	63	58	55		62	58	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87319
5°	81446
10°	70208
15°	60758
20°	52856
25°	45422
30°	35692
35°	20825
40°	9609
45°	4971
50°	2495
55°	1215
60°	617
65°	365
70°	171
75°	155
80°	107
85°	0



TEST NUMBER: P244358

CATALOG NUMBER: LSR8B20D010 EC8B20950 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.1	12.8
10°-20°	532.1	28.7
20°-30°	605.0	32.6
30°-40°	355.3	19.2
40°-50°	95.4	5.1
50°-60°	22.6	1.2
60°-70°	5.1	0.3
70°-80°	1.2	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1375.3	74.1
0°-40°	1730.6	93.3
0°-60°	1848.6	99.7
0°-90°	1855.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1855.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2832	
5°	2631	238
15°	1903	532
25°	1335	605
35°	553	355
45°	114	95
55°	23	23
65°	5	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P244358

CATALOG NUMBER: LSR8B20D010 EC8B20950 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2831.7
1°	2816.0
2°	2787.2
3°	2746.5
4°	2693.8
5°	2631.2
6°	2560.4
7°	2480.2
8°	2400.0
9°	2319.2
10°	2242.2
11°	2167.0
12°	2096.2
13°	2030.4
14°	1964.6
15°	1903.2
16°	1843.1
17°	1783.6
18°	1725.9
19°	1667.7
20°	1610.7
21°	1553.7
22°	1499.2
23°	1445.3
24°	1390.2
25°	1335.0
26°	1278.0
27°	1216.0
28°	1150.8
29°	1079.4
30°	1002.4
32.5°	786.2
35°	553.2
37.5°	364.6
40°	238.7
42.5°	164.8
45°	114.0
47.5°	78.3
50°	52.0
52.5°	33.8
55°	22.6
57.5°	15.0
60°	10.0
62.5°	6.9
65°	5.0



TEST NUMBER: P244358

CATALOG NUMBER: LSR8B20D010 EC8B20950 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	3.1
70°	1.9
72.5°	1.3
75°	1.3
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)