

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251103

Luminaire Tested: **LSR8B70D010 EC8B709730 8LBS0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251103
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B70D010 EC8B709730 8LBS0WMH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5961.0 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251103

CATALOG NUMBER: LSR8B70D010 EC8B709730 8LBS0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P251103

CATALOG NUMBER: LSR8B70D010 EC8B709730 8LBS0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P251103

CATALOG NUMBER: LSR8B70D010 EC8B709730 8LBS0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	318.2	5.3
10°-20°	900.6	15.1
20°-30°	1340.8	22.5
30°-40°	1523.1	25.6
40°-50°	1245.0	20.9
50°-60°	487.9	8.2
60°-70°	113.7	1.9
70°-80°	27.4	0.5
80°-90°	4.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2559.6	42.9
0°-40°	4082.7	68.5
0°-60°	5815.5	97.6
0°-90°	5961.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5961.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3380	
5°	3356	318
15°	3193	901
25°	2917	1341
35°	2447	1523
45°	1653	1245
55°	507	488
65°	106	114
75°	25	27
85°	4	4
90°	0	



TEST NUMBER: P251103

CATALOG NUMBER: LSR8B70D010 EC8B709730 8LBS0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3379.8
2.5°	3374.4
5°	3356.5
7.5°	3326.0
10°	3288.4
12.5°	3241.7
15°	3193.3
17.5°	3135.9
20°	3073.2
22.5°	2999.7
25°	2917.2
27.5°	2820.4
30°	2711.0
32.5°	2587.3
35°	2447.4
37.5°	2293.2
40°	2121.1
42.5°	1913.1
45°	1653.1
47.5°	1348.3
50°	1031.0
52.5°	740.5
55°	507.4
57.5°	331.7
60°	222.3
62.5°	152.4
65°	105.8
67.5°	69.9
70°	46.6
72.5°	32.3
75°	25.1
77.5°	17.9
80°	10.8
82.5°	5.4
85°	3.6
87.5°	1.8
90°	0.0

(END OF REPORT)