

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250295

Luminaire Tested: **LSR8B80D010 EC8B80830 8LBN0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250295  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B80D010 EC8B80830 8LBN0GPH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 3000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6524.0 lumens  
Efficiency: N/A  
Efficacy: 87.7 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250295

CATALOG NUMBER: LSR8B80D010 EC8B80830 8LBN0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P250295

CATALOG NUMBER: LSR8B80D010 EC8B80830 8LBN0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	321459
5°	316323
10°	281047
15°	231839
20°	195254
25°	164687
30°	123306
35°	69785
40°	27594
45°	7409
50°	1420
55°	0
60°	204
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250295

CATALOG NUMBER: LSR8B80D010 EC8B80830 8LBN0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	935.8	14.3
10°-20°	2034.0	31.2
20°-30°	2183.6	33.5
30°-40°	1180.2	18.1
40°-50°	184.1	2.8
50°-60°	5.0	0.1
60°-70°	1.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5153.4	79.0
0°-40°	6333.6	97.1
0°-60°	6522.8	100.0
0°-90°	6524.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6524.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10425	
5°	10219	936
15°	7262	2034
25°	4840	2184
35°	1854	1180
45°	170	184
55°	0	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250295

CATALOG NUMBER: LSR8B80D010 EC8B80830 8LBN0GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10424.7
1°	10444.5
2°	10434.7
3°	10398.9
4°	10330.3
5°	10219.1
6°	10066.0
7°	9860.1
8°	9602.3
9°	9305.6
10°	8975.7
11°	8629.6
12°	8270.6
13°	7911.9
14°	7578.6
15°	7262.2
16°	6971.6
17°	6690.9
18°	6429.8
19°	6185.3
20°	5950.1
21°	5721.5
22°	5506.0
23°	5290.9
24°	5065.7
25°	4840.3
26°	4611.7
27°	4350.8
28°	4063.4
29°	3770.0
30°	3463.0
31°	3133.4
32°	2803.5
33°	2477.2
34°	2147.6
35°	1853.8
37.5°	1184.8
40°	685.5
42.5°	365.7
45°	169.9
47.5°	91.6
50°	29.6
52.5°	3.3
55°	0.0
57.5°	3.3



TEST NUMBER: P250295

CATALOG NUMBER: LSR8B80D010 EC8B80830 8LBN0GPH

**CANDELA DISTRIBUTION (continued):**

	0°
60°	3.3
62.5°	0.0
65°	0.0
67.5°	3.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)