

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244065

Luminaire Tested: **LSR8B30D010 EC8B30940 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244065
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30940 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 4000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3106.0 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244065

CATALOG NUMBER: LSR8B30D010 EC8B30940 8LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P244065

CATALOG NUMBER: LSR8B30D010 EC8B30940 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88	91	88	86	88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63	71	66	62	69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47	56	51	46	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53402
5°	53634
10°	54505
15°	55883
20°	56859
25°	56922
30°	55158
35°	50503
40°	43893
45°	34730
50°	22523
55°	11252
60°	4724
65°	2080
70°	640
75°	322
80°	320
85°	318



TEST NUMBER: P244065

CATALOG NUMBER: LSR8B30D010 EC8B30940 8LBS0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.6	5.3
10°-20°	494.7	15.9
20°-30°	766.3	24.7
30°-40°	832.2	26.8
40°-50°	604.7	19.5
50°-60°	205.5	6.6
60°-70°	32.7	1.1
70°-80°	3.5	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1426.6	45.9
0°-40°	2258.8	72.7
0°-60°	3069.0	98.8
0°-90°	3106.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3106.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1732	
5°	1733	166
15°	1750	495
25°	1673	766
35°	1342	832
45°	796	605
55°	209	206
65°	28	33
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P244065

CATALOG NUMBER: LSR8B30D010 EC8B30940 8LBSOLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1731.8
2.5°	1731.8
5°	1732.7
7.5°	1735.3
10°	1740.7
12.5°	1746.9
15°	1750.5
17.5°	1746.9
20°	1732.7
22.5°	1706.8
25°	1673.0
27.5°	1622.2
30°	1549.1
32.5°	1452.0
35°	1341.6
37.5°	1221.3
40°	1090.4
42.5°	948.7
45°	796.4
47.5°	632.5
50°	469.5
52.5°	321.6
55°	209.3
57.5°	127.4
60°	76.6
62.5°	47.2
65°	28.5
67.5°	16.0
70°	7.1
72.5°	4.5
75°	2.7
77.5°	1.8
80°	1.8
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)