

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250386

Luminaire Tested: **LSR8B80D010 EC8B80835 8LBN0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250386  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B80D010 EC8B80835 8LBN0B  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 3500 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4943.0 lumens  
Efficiency: N/A  
Efficacy: 66.4 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250386

CATALOG NUMBER: LSR8B80D010 EC8B80835 8LBN0B

### Luminous Intensity Polar Plot





TEST NUMBER: P250386

CATALOG NUMBER: LSR8B80D010 EC8B80835 8LBN0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	243558
5°	239665
10°	212937
15°	175656
20°	147938
25°	124777
30°	93425
35°	52871
40°	20904
45°	5612
50°	1075
55°	0
60°	154
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250386

CATALOG NUMBER: LSR8B80D010 EC8B80835 8LBN0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	709.0	14.3
10°-20°	1541.1	31.2
20°-30°	1654.4	33.5
30°-40°	894.2	18.1
40°-50°	139.5	2.8
50°-60°	3.8	0.1
60°-70°	0.9	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3904.5	79.0
0°-40°	4798.7	97.1
0°-60°	4942.1	100.0
0°-90°	4943.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4943.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7898	
5°	7743	709
15°	5502	1541
25°	3667	1654
35°	1404	894
45°	129	140
55°	0	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250386

CATALOG NUMBER: LSR8B80D010 EC8B80835 8LBN0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7898.4
1°	7913.4
2°	7906.0
3°	7878.9
4°	7826.9
5°	7742.6
6°	7626.7
7°	7470.6
8°	7275.3
9°	7050.5
10°	6800.5
11°	6538.3
12°	6266.3
13°	5994.6
14°	5742.1
15°	5502.3
16°	5282.2
17°	5069.5
18°	4871.6
19°	4686.4
20°	4508.2
21°	4335.0
22°	4171.7
23°	4008.7
24°	3838.1
25°	3667.3
26°	3494.2
27°	3296.4
28°	3078.7
29°	2856.4
30°	2623.8
31°	2374.1
32°	2124.1
33°	1876.9
34°	1627.2
35°	1404.5
37.5°	897.7
40°	519.3
42.5°	277.1
45°	128.7
47.5°	69.4
50°	22.4
52.5°	2.5
55°	0.0
57.5°	2.5



TEST NUMBER: P250386

CATALOG NUMBER: LSR8B80D010 EC8B80835 8LBN0B

**CANDELA DISTRIBUTION (continued):**

	0°
60°	2.5
62.5°	0.0
65°	0.0
67.5°	2.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)