

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250057

Luminaire Tested: **LSR8B80D010 EC8B80840 8LBN0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250057  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13946)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B80D010 EC8B80840 8LBN0WH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 4000 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7726.0 lumens  
Efficiency: N/A  
Efficacy: 103.8 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.66  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250057

CATALOG NUMBER: LSR8B80D010 EC8B80840 8LBN0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P250057

CATALOG NUMBER: LSR8B80D010 EC8B80840 8LBN0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	89
3	105	99	94	91	103	97	93	90	95	91	89		92	90	87		90	88	86	85
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86	84	81	80
5	96	88	83	79	94	87	83	79	86	82	78		84	81	78		83	80	77	76
6	92	84	79	75	90	83	78	74	82	77	74		80	76	74		79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70		77	73	70		76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	67		73	69	66		72	69	66	65
9	81	72	67	64	80	72	67	64	71	66	63		70	66	63		69	66	63	62
10	78	69	64	61	77	69	64	61	68	63	60		67	63	60		67	63	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	478922
5°	463145
10°	393874
15°	300623
20°	229750
25°	178038
30°	121430
35°	71343
40°	21814
45°	8582
50°	130
55°	145
60°	167
65°	394
70°	730
75°	643
80°	479
85°	2866



TEST NUMBER: P250057

CATALOG NUMBER: LSR8B80D010 EC8B80840 8LBN0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1356.4	17.6
10°-20°	2628.4	34.0
20°-30°	2366.4	30.6
30°-40°	1170.8	15.2
40°-50°	178.1	2.3
50°-60°	7.3	0.1
60°-70°	9.4	0.1
70°-80°	3.5	0.0
80°-90°	5.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6351.3	82.2
0°-40°	7522.1	97.4
0°-60°	7707.5	99.8
0°-90°	7726.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7726.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	15531	
5°	14962	###
15°	9417	2628
25°	5233	2366
35°	1895	1171
45°	197	178
55°	3	7
65°	5	9
75°	5	4
85°	8	6
90°	0	



TEST NUMBER: P250057

CATALOG NUMBER: LSR8B80D010 EC8B80840 8LBNOWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	15531.1
1°	15498.8
2°	15506.8
3°	15428.6
4°	15285.8
5°	14962.3
6°	14714.3
7°	14320.7
8°	13792.3
9°	13242.3
10°	12579.0
11°	11986.0
12°	11349.8
13°	10646.1
14°	10039.6
15°	9416.8
16°	8885.7
17°	8416.6
18°	7839.7
19°	7416.4
20°	7001.3
21°	6569.9
22°	6254.5
23°	5887.8
24°	5550.8
25°	5232.7
26°	4858.0
27°	4521.1
28°	4219.1
29°	3887.5
30°	3410.3
31°	3140.8
32°	2801.0
33°	2429.0
34°	2145.9
35°	1895.2
37.5°	1199.6
40°	541.9
42.5°	369.4
45°	196.8
47.5°	110.5
50°	2.7
52.5°	10.8
55°	2.7
57.5°	16.2



TEST NUMBER: P250057

CATALOG NUMBER: LSR8B80D010 EC8B80840 8LBN0WH

**CANDELA DISTRIBUTION (continued):**

	0°
60°	2.7
62.5°	13.5
65°	5.4
67.5°	13.5
70°	8.1
72.5°	2.7
75°	5.4
77.5°	0.0
80°	2.7
82.5°	10.8
85°	8.1
87.5°	0.0
90°	0.0

(END OF REPORT)