

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246526

Luminaire Tested: **LSR8B40D010 EC8B40927 8LBS0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246526  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B40D010 EC8B40927 8LBS0B  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 2700 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2792.0 lumens  
Efficiency: N/A  
Efficacy: 68.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246526

CATALOG NUMBER: LSR8B40D010 EC8B40927 8LBS0B

### Luminous Intensity Polar Plot





TEST NUMBER: P246526

CATALOG NUMBER: LSR8B40D010 EC8B40927 8LBS0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	94	90	103	98	93	89	94	90	87		91	88	85		88	86	84	82
3	98	90	84	79	96	89	83	79	86	81	77		84	80	76		81	78	75	73
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75	71	67	66
5	86	75	68	63	84	74	68	63	72	66	62		71	65	61		69	64	61	59
6	80	69	62	56	78	68	61	56	67	60	56		65	60	55		64	59	55	53
7	75	63	56	51	73	63	56	51	61	55	51		60	54	50		59	54	50	48
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		54	49	46	44
9	66	54	47	42	65	54	47	42	53	46	42		52	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39		48	42	38		47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P246526

CATALOG NUMBER: LSR8B40D010 EC8B40927 8LBS0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.7	5.5
10°-20°	434.4	15.6
20°-30°	646.6	23.2
30°-40°	732.4	26.2
40°-50°	592.1	21.2
50°-60°	205.4	7.4
60°-70°	28.1	1.0
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1233.7	44.2
0°-40°	1966.1	70.4
0°-60°	2763.6	99.0
0°-90°	2792.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2792.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1617	
5°	1610	153
15°	1541	434
25°	1407	647
35°	1177	732
45°	789	592
55°	209	205
65°	24	28
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246526

CATALOG NUMBER: LSR8B40D010 EC8B40927 8LBS0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1617.4
2.5°	1615.4
5°	1609.5
7.5°	1597.6
10°	1582.7
12.5°	1562.9
15°	1541.1
17.5°	1513.4
20°	1482.7
22.5°	1447.0
25°	1407.4
27.5°	1359.9
30°	1305.4
32.5°	1244.0
35°	1176.7
37.5°	1102.4
40°	1019.2
42.5°	917.2
45°	789.4
47.5°	634.9
50°	474.4
52.5°	324.9
55°	209.0
57.5°	123.8
60°	72.3
62.5°	42.6
65°	23.8
67.5°	10.9
70°	3.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)