

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250533

Luminaire Tested: **LSR8B80D010 EC8B809730 8LBM0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250533  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14005)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B80D010 EC8B809730 8LBM0GPH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 3000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5396.0 lumens  
Efficiency: N/A  
Efficacy: 72.5 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250533

CATALOG NUMBER: LSR8B80D010 EC8B809730 8LBM0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P250533

CATALOG NUMBER: LSR8B80D010 EC8B809730 8LBM0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250533

CATALOG NUMBER: LSR8B80D010 EC8B809730 8LBM0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	609.3	11.3
10°-20°	1448.6	26.8
20°-30°	1804.7	33.4
30°-40°	1217.3	22.6
40°-50°	287.8	5.3
50°-60°	21.0	0.4
60°-70°	3.8	0.1
70°-80°	2.8	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3862.6	71.6
0°-40°	5080.0	94.1
0°-60°	5388.8	99.9
0°-90°	5396.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5396.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6844	
5°	6645	609
15°	5144	1449
25°	4001	1805
35°	1951	1217
45°	313	288
55°	9	21
65°	0	4
75°	7	3
85°	2	1
90°	0	



TEST NUMBER: P250533

CATALOG NUMBER: LSR8B80D010 EC8B809730 8LBM0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6843.5
2.5°	6831.9
5°	6645.1
7.5°	6306.7
10°	5888.9
12.5°	5494.5
15°	5144.4
17.5°	4843.2
20°	4565.5
22.5°	4299.4
25°	4000.7
27.5°	3610.9
30°	3134.7
32.5°	2558.2
35°	1951.3
37.5°	1395.8
40°	910.3
42.5°	543.9
45°	312.7
47.5°	175.0
50°	86.4
52.5°	39.7
55°	9.3
57.5°	2.3
60°	4.7
62.5°	7.0
65°	0.0
67.5°	4.7
70°	2.3
72.5°	2.3
75°	7.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	2.3
87.5°	0.0
90°	0.0

(END OF REPORT)