

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244799

Luminaire Tested: **LSR8B50D010 EC8B50927 8LBN0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244799  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B50D010 EC8B50927 8LBN0WMH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 2700 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3790.2 lumens  
Efficiency: N/A  
Efficacy: 71.5 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 53  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244799

CATALOG NUMBER: LSR8B50D010 EC8B50927 8LBN0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244799

CATALOG NUMBER: LSR8B50D010 EC8B50927 8LBN0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  | 0   |     |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 |  | 101 | 100 | 99  |  | 98  | 97  | 96  | 94  |
| 2   | 108 | 104 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 96  | 93  |  | 96  | 94  | 91  |  | 93  | 91  | 90  | 88  |
| 3   | 103 | 97  | 92  | 89  | 101 | 96  | 91  | 88  | 93  | 89  | 86  |  | 91  | 88  | 85  |  | 89  | 86  | 84  | 82  |
| 4   | 98  | 91  | 86  | 82  | 97  | 90  | 85  | 81  | 88  | 84  | 80  |  | 86  | 82  | 79  |  | 84  | 81  | 79  | 77  |
| 5   | 94  | 86  | 80  | 76  | 92  | 85  | 80  | 76  | 83  | 78  | 75  |  | 81  | 77  | 74  |  | 80  | 76  | 74  | 72  |
| 6   | 89  | 81  | 75  | 71  | 88  | 80  | 75  | 71  | 79  | 74  | 70  |  | 77  | 73  | 70  |  | 76  | 72  | 69  | 68  |
| 7   | 85  | 76  | 71  | 67  | 84  | 76  | 70  | 66  | 74  | 70  | 66  |  | 73  | 69  | 66  |  | 72  | 68  | 65  | 64  |
| 8   | 81  | 72  | 66  | 63  | 80  | 72  | 66  | 62  | 71  | 66  | 62  |  | 70  | 65  | 62  |  | 69  | 65  | 62  | 60  |
| 9   | 78  | 68  | 63  | 59  | 77  | 68  | 63  | 59  | 67  | 62  | 59  |  | 66  | 62  | 59  |  | 65  | 61  | 58  | 57  |
| 10  | 74  | 65  | 59  | 56  | 73  | 65  | 59  | 56  | 64  | 59  | 56  |  | 63  | 59  | 55  |  | 62  | 58  | 55  | 54  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P244799

CATALOG NUMBER: LSR8B50D010 EC8B50927 8LBN0WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 500.7  | 13.2      |
| 10°-20°   | 1150.8 | 30.4      |
| 20°-30°   | 1221.0 | 32.2      |
| 30°-40°   | 696.7  | 18.4      |
| 40°-50°   | 172.7  | 4.6       |
| 50°-60°   | 33.9   | 0.9       |
| 60°-70°   | 10.2   | 0.3       |
| 70°-80°   | 2.3    | 0.1       |
| 80°-90°   | 1.9    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2872.5 | 75.8      |
| 0°-40°    | 3569.2 | 94.2      |
| 0°-60°    | 3775.8 | 99.6      |
| 0°-90°    | 3790.2 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3790.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | Flux |
|------|------|------|
| 0°   | 5520 |      |
| 5°   | 5422 | 501  |
| 15°  | 4130 | 1151 |
| 25°  | 2695 | 1221 |
| 35°  | 1089 | 697  |
| 45°  | 195  | 173  |
| 55°  | 31   | 34   |
| 65°  | 8    | 10   |
| 75°  | 0    | 2    |
| 85°  | 3    | 2    |
| 90°  | 0    | 0    |
| 95°  | 0    | 0    |
| 105° | 0    | 0    |
| 115° | 0    | 0    |
| 125° | 0    | 0    |
| 135° | 0    | 0    |
| 145° | 0    | 0    |
| 155° | 0    | 0    |
| 165° | 0    | 0    |
| 175° | 0    | 0    |
| 180° | 0    | 0    |



TEST NUMBER: P244799

CATALOG NUMBER: LSR8B50D010 EC8B50927 8LBN0WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°     |        |
|--------|--------|
| 0°     | 5519.7 |
| 2.5°   | 5517.1 |
| 5°     | 5422.0 |
| 7.5°   | 5213.1 |
| 10°    | 4904.3 |
| 12.5°  | 4531.5 |
| 15°    | 4130.0 |
| 17.5°  | 3747.3 |
| 20°    | 3383.3 |
| 22.5°  | 3033.2 |
| 25°    | 2695.4 |
| 27.5°  | 2332.6 |
| 30°    | 1932.4 |
| 32.5°  | 1502.1 |
| 35°    | 1089.4 |
| 37.5°  | 750.5  |
| 40°    | 485.2  |
| 42.5°  | 307.7  |
| 45°    | 195.2  |
| 47.5°  | 127.7  |
| 50°    | 80.1   |
| 52.5°  | 48.7   |
| 55°    | 31.4   |
| 57.5°  | 25.1   |
| 60°    | 16.2   |
| 62.5°  | 15.0   |
| 65°    | 7.5    |
| 67.5°  | 7.5    |
| 70°    | 6.3    |
| 72.5°  | 3.7    |
| 75°    | 0.0    |
| 77.5°  | 1.2    |
| 80°    | 1.2    |
| 82.5°  | 2.6    |
| 85°    | 2.6    |
| 87.5°  | 1.2    |
| 90°    | 0.0    |
| 92.5°  | 0.0    |
| 95°    | 0.0    |
| 97.5°  | 0.0    |
| 100°   | 0.0    |
| 102.5° | 0.0    |
| 105°   | 0.0    |
| 107.5° | 0.0    |
| 110°   | 0.0    |



TEST NUMBER: P244799

CATALOG NUMBER: LSR8B50D010 EC8B50927 8LBN0WMH

**CANDELA DISTRIBUTION (continued):**

|        | 0°  |
|--------|-----|
| 112.5° | 0.0 |
| 115°   | 0.0 |
| 117.5° | 0.0 |
| 120°   | 0.0 |
| 122.5° | 0.0 |
| 125°   | 0.0 |
| 127.5° | 0.0 |
| 130°   | 0.0 |
| 132.5° | 0.0 |
| 135°   | 0.0 |
| 137.5° | 0.0 |
| 140°   | 0.0 |
| 142.5° | 0.0 |
| 145°   | 0.0 |
| 147.5° | 0.0 |
| 150°   | 0.0 |
| 152.5° | 0.0 |
| 155°   | 0.0 |
| 157.5° | 0.0 |
| 160°   | 0.0 |
| 162.5° | 0.0 |
| 165°   | 0.0 |
| 167.5° | 0.0 |
| 170°   | 0.0 |
| 172.5° | 0.0 |
| 175°   | 0.0 |
| 177.5° | 0.0 |
| 180°   | 0.0 |

(END OF REPORT)