

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249960

Luminaire Tested: **LSR8B90D010 EC8B90830 8LBN0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P249960  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13951)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B90D010 EC8B90830 8LBN0WMH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 3000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7986.0 lumens  
Efficiency: N/A  
Efficacy: 92.8 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 86.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P249960

CATALOG NUMBER: LSR8B90D010 EC8B90830 8LBN0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P249960

CATALOG NUMBER: LSR8B90D010 EC8B90830 8LBN0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59	66	62	58	65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	358682
5°	353685
10°	323572
15°	277813
20°	233947
25°	193294
30°	144987
35°	86424
40°	41176
45°	17936
50°	8131
55°	3586
60°	2054
65°	1219
70°	1253
75°	0
80°	497
85°	1981



TEST NUMBER: P249960

CATALOG NUMBER: LSR8B90D010 EC8B90830 8LBN0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1055.7	13.2
10°-20°	2422.2	30.3
20°-30°	2573.3	32.2
30°-40°	1468.2	18.4
40°-50°	364.0	4.6
50°-60°	71.6	0.9
60°-70°	21.6	0.3
70°-80°	5.1	0.1
80°-90°	4.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6051.3	75.8
0°-40°	7519.5	94.2
0°-60°	7955.1	99.6
0°-90°	7986.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7986.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11632	
5°	11426	###
15°	8702	2422
25°	5681	2573
35°	2296	1468
45°	411	364
55°	67	72
65°	17	22
75°	0	5
85°	6	4
90°	0	



TEST NUMBER: P249960

CATALOG NUMBER: LSR8B90D010 EC8B90830 8LBN0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11631.8
1°	11654.1
2°	11645.7
3°	11604.0
4°	11531.8
5°	11426.1
6°	11287.2
7°	11095.4
8°	10875.8
9°	10617.4
10°	10333.8
11°	10033.7
12°	9711.2
13°	9383.3
14°	9047.0
15°	8702.3
16°	8377.1
17°	8049.2
18°	7740.6
19°	7426.6
20°	7129.2
22.5°	6392.6
25°	5681.1
27.5°	4916.8
30°	4071.9
32.5°	3165.7
35°	2295.8
37.5°	1581.5
40°	1022.9
42.5°	647.7
45°	411.3
47.5°	269.7
50°	169.5
52.5°	102.9
55°	66.7
57.5°	52.8
60°	33.3
62.5°	30.5
65°	16.7
67.5°	16.7
70°	13.9
72.5°	8.4
75°	0.0
77.5°	2.8
80°	2.8



TEST NUMBER: P249960

CATALOG NUMBER: LSR8B90D010 EC8B90830 8LBN0WMH

**CANDELA DISTRIBUTION (continued):**

	0°
82.5°	5.6
85°	5.6
87.5°	2.8
90°	0.0

(END OF REPORT)