

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245363

Luminaire Tested: **LSR8B50D010 EC8B50940 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245363
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B50D010 EC8B50940 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 4000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5477.1 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245363

CATALOG NUMBER: LSR8B50D010 EC8B50940 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245363

CATALOG NUMBER: LSR8B50D010 EC8B50940 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99 | 99 | 97 | 96 | 96 | 94 | 93 | 91 |
| 2 | 105 | 100 | 95 | 91 | 103 | 98 | 93 | 90 | 94 | 91 | 88 | 91 | 88 | 86 | 89 | 86 | 84 | 82 |
| 3 | 99 | 91 | 85 | 80 | 96 | 89 | 84 | 79 | 87 | 82 | 78 | 84 | 80 | 77 | 82 | 78 | 76 | 74 |
| 4 | 92 | 83 | 76 | 71 | 90 | 82 | 76 | 71 | 79 | 74 | 70 | 77 | 73 | 69 | 75 | 71 | 68 | 66 |
| 5 | 86 | 76 | 69 | 64 | 84 | 75 | 68 | 63 | 73 | 67 | 63 | 71 | 66 | 62 | 70 | 65 | 62 | 60 |
| 6 | 80 | 70 | 63 | 57 | 79 | 69 | 62 | 57 | 67 | 61 | 57 | 66 | 60 | 56 | 64 | 60 | 56 | 54 |
| 7 | 75 | 64 | 57 | 52 | 74 | 63 | 57 | 52 | 62 | 56 | 51 | 61 | 55 | 51 | 60 | 55 | 51 | 49 |
| 8 | 71 | 59 | 52 | 47 | 69 | 59 | 52 | 47 | 57 | 51 | 47 | 56 | 51 | 47 | 55 | 50 | 46 | 45 |
| 9 | 66 | 55 | 48 | 43 | 65 | 54 | 48 | 43 | 53 | 47 | 43 | 52 | 47 | 43 | 51 | 46 | 43 | 41 |
| 10 | 63 | 51 | 44 | 40 | 61 | 51 | 44 | 40 | 50 | 44 | 39 | 49 | 43 | 39 | 48 | 43 | 39 | 38 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 95660 |
| 5° | 96026 |
| 10° | 97236 |
| 15° | 99137 |
| 20° | 100553 |
| 25° | 100967 |
| 30° | 97872 |
| 35° | 89330 |
| 40° | 77276 |
| 45° | 60835 |
| 50° | 39242 |
| 55° | 19263 |
| 60° | 7919 |
| 65° | 3473 |
| 70° | 1001 |
| 75° | 381 |
| 80° | 284 |
| 85° | 0 |



TEST NUMBER: P245363

CATALOG NUMBER: LSR8B50D010 EC8B50940 8LBS0WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 296.2 | 5.4 |
| 10°-20° | 877.6 | 16.0 |
| 20°-30° | 1358.8 | 24.8 |
| 30°-40° | 1472.0 | 26.9 |
| 40°-50° | 1059.2 | 19.3 |
| 50°-60° | 354.4 | 6.5 |
| 60°-70° | 53.6 | 1.0 |
| 70°-80° | 4.6 | 0.1 |
| 80°-90° | 0.7 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2532.6 | 46.2 |
| 0°-40° | 4004.6 | 73.1 |
| 0°-60° | 5418.2 | 98.9 |
| 0°-90° | 5477.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 5477.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3102 | |
| 5° | 3102 | 296 |
| 15° | 3105 | 878 |
| 25° | 2968 | 1359 |
| 35° | 2373 | 1472 |
| 45° | 1395 | 1059 |
| 55° | 358 | 354 |
| 65° | 48 | 54 |
| 75° | 3 | 5 |
| 85° | 0 | 1 |
| 90° | 0 | |



TEST NUMBER: P245363

CATALOG NUMBER: LSR8B50D010 EC8B50940 8LBS0WH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 3102.2 |
| 2.5° | 3102.2 |
| 5° | 3102.2 |
| 7.5° | 3103.8 |
| 10° | 3105.4 |
| 12.5° | 3108.6 |
| 15° | 3105.4 |
| 17.5° | 3092.7 |
| 20° | 3064.2 |
| 22.5° | 3021.4 |
| 25° | 2967.5 |
| 27.5° | 2881.9 |
| 30° | 2748.7 |
| 32.5° | 2574.4 |
| 35° | 2373.0 |
| 37.5° | 2155.9 |
| 40° | 1919.7 |
| 42.5° | 1666.0 |
| 45° | 1395.0 |
| 47.5° | 1101.7 |
| 50° | 818.0 |
| 52.5° | 561.2 |
| 55° | 358.3 |
| 57.5° | 214.0 |
| 60° | 128.4 |
| 62.5° | 77.7 |
| 65° | 47.6 |
| 67.5° | 23.8 |
| 70° | 11.1 |
| 72.5° | 4.8 |
| 75° | 3.2 |
| 77.5° | 3.2 |
| 80° | 1.6 |
| 82.5° | 1.6 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)