

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244073

Luminaire Tested: **LSR8B50D010 EC8B50950 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244073
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B50D010 EC8B50950 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5723.0 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244073

CATALOG NUMBER: LSR8B50D010 EC8B50950 8LBS0LI

Luminous Intensity Polar Plot





TEST NUMBER: P244073

CATALOG NUMBER: LSR8B50D010 EC8B50950 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88		91	88	86		88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78		84	80	77		82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63		71	66	62		69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56		66	60	56		64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51		61	55	51		59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47		56	51	46		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39		49	43	39		48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98396
5°	98821
10°	100427
15°	102968
20°	104763
25°	104883
30°	101636
35°	93056
40°	80874
45°	63992
50°	41496
55°	20736
60°	8708
65°	3831
70°	1181
75°	584
80°	586
85°	566



TEST NUMBER: P244073

CATALOG NUMBER: LSR8B50D010 EC8B50950 8LBS0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	305.2	5.3
10°-20°	911.4	15.9
20°-30°	1411.9	24.7
30°-40°	1533.4	26.8
40°-50°	1114.2	19.5
50°-60°	378.7	6.6
60°-70°	60.3	1.1
70°-80°	6.5	0.1
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2628.6	45.9
0°-40°	4161.9	72.7
0°-60°	5654.9	98.8
0°-90°	5723.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5723.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3191	
5°	3192	305
15°	3225	911
25°	3083	1412
35°	2472	1533
45°	1467	1114
55°	386	379
65°	52	60
75°	5	6
85°	2	1
90°	0	



TEST NUMBER: P244073

CATALOG NUMBER: LSR8B50D010 EC8B50950 8LBS0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3190.9
2.5°	3190.9
5°	3192.5
7.5°	3197.5
10°	3207.3
12.5°	3218.8
15°	3225.4
17.5°	3218.8
20°	3192.5
22.5°	3144.9
25°	3082.6
27.5°	2989.0
30°	2854.4
32.5°	2675.5
35°	2472.0
37.5°	2250.4
40°	2009.1
42.5°	1748.1
45°	1467.4
47.5°	1165.4
50°	865.0
52.5°	592.5
55°	385.7
57.5°	234.7
60°	141.2
62.5°	87.0
65°	52.5
67.5°	29.5
70°	13.1
72.5°	8.2
75°	4.9
77.5°	3.3
80°	3.3
82.5°	1.6
85°	1.6
87.5°	0.0
90°	0.0

(END OF REPORT)