

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251056

Luminaire Tested: **LSR8B60D010 EC8B60827 8LBM0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251056
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60827 8LBM0WMH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 2700 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5595.9 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251056

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBM0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P251056

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBM0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82				82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76				76
5	93	85	79	75	92	84	79	75	82	78	74	81	77	73	79	76	73	71				71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67				67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63				63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59				59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53				53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216622
5°	220780
10°	210501
15°	185869
20°	161071
25°	136100
30°	102280
35°	68482
40°	38350
45°	15407
50°	5335
55°	1478
60°	839
65°	730
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P251056

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBM0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	667.3	11.9
10°-20°	1624.0	29.0
20°-30°	1802.1	32.2
30°-40°	1141.7	20.4
40°-50°	316.8	5.7
50°-60°	36.3	0.6
60°-70°	7.1	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4093.4	73.1
0°-40°	5235.0	93.6
0°-60°	5588.1	99.9
0°-90°	5595.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5595.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7025	
5°	7132	667
15°	5822	1624
25°	4000	1802
35°	1819	1142
45°	353	317
55°	28	36
65°	10	7
75°	0	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251056

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBM0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	7024.9
2.5°	7076.8
5°	7132.5
7.5°	7021.3
10°	6722.7
12.5°	6296.7
15°	5822.2
17.5°	5356.3
20°	4908.4
22.5°	4468.9
25°	4000.1
27.5°	3451.9
30°	2872.5
32.5°	2311.2
35°	1819.2
37.5°	1374.7
40°	952.7
42.5°	592.5
45°	353.3
47.5°	203.1
50°	111.2
52.5°	54.4
55°	27.5
57.5°	20.7
60°	13.6
62.5°	7.1
65°	10.0
67.5°	5.0
70°	0.0
72.5°	1.4
75°	0.0
77.5°	1.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251056

CATALOG NUMBER: LSR8B60D010 EC8B60827 8LBM0WMH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)