

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250114

Luminaire Tested: **LSR8B90D010 EC8B909730 8LBN0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13946)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B90D010 EC8B909730 8LBN0WH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6452.0 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.66
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 86.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250114

CATALOG NUMBER: LSR8B90D010 EC8B909730 8LBN0WH

Luminous Intensity Polar Plot





TEST NUMBER: P250114

CATALOG NUMBER: LSR8B90D010 EC8B909730 8LBN0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89
3	105	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76
6	92	84	79	75	90	83	78	74	82	77	74	80	76	74	79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	72	69	66	65
9	81	72	67	64	80	72	67	64	71	66	63	70	66	63	69	66	63	62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250114

CATALOG NUMBER: LSR8B90D010 EC8B909730 8LBN0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1132.8	17.6
10°-20°	2195.0	34.0
20°-30°	1976.2	30.6
30°-40°	977.8	15.2
40°-50°	148.7	2.3
50°-60°	6.1	0.1
60°-70°	7.9	0.1
70°-80°	3.0	0.0
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5304.0	82.2
0°-40°	6281.7	97.4
0°-60°	6436.6	99.8
0°-90°	6452.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6452.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12970	
5°	12495	###
15°	7864	2195
25°	4370	1976
35°	1583	978
45°	164	149
55°	2	6
65°	4	8
75°	4	3
85°	7	5
90°	0	



TEST NUMBER: P250114

CATALOG NUMBER: LSR8B90D010 EC8B909730 8LBN0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	12970.1
1°	12943.1
2°	12949.8
3°	12884.5
4°	12765.2
5°	12495.1
6°	12287.9
7°	11959.3
8°	11518.0
9°	11058.7
10°	10504.8
11°	10009.5
12°	9478.2
13°	8890.6
14°	8384.1
15°	7864.0
16°	7420.4
17°	7028.7
18°	6546.9
19°	6193.4
20°	5846.8
21°	5486.5
22°	5223.1
23°	4917.0
24°	4635.5
25°	4369.9
26°	4056.9
27°	3775.6
28°	3523.4
29°	3246.4
30°	2848.0
31°	2622.9
32°	2339.2
33°	2028.4
34°	1792.1
35°	1582.7
37.5°	1001.8
40°	452.6
42.5°	308.4
45°	164.3
47.5°	92.3
50°	2.3
52.5°	9.0
55°	2.3
57.5°	13.5



TEST NUMBER: P250114

CATALOG NUMBER: LSR8B90D010 EC8B909730 8LBN0WH

CANDELA DISTRIBUTION (continued):

	0°
60°	2.3
62.5°	11.3
65°	4.5
67.5°	11.3
70°	6.8
72.5°	2.3
75°	4.5
77.5°	0.0
80°	2.3
82.5°	9.0
85°	6.8
87.5°	0.0
90°	0.0

(END OF REPORT)