

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251176

Luminaire Tested: **LSR8B60D010 EC8B60830 8LBS0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251176  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60830 8LBS0WH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 3000 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6699.0 lumens  
Efficiency: N/A  
Efficacy: 112.6 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251176

CATALOG NUMBER: LSR8B60D010 EC8B60830 8LBS0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P251176

CATALOG NUMBER: LSR8B60D010 EC8B60830 8LBS0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	117005
5°	117452
10°	118932
15°	121257
20°	122989
25°	123494
30°	119710
35°	109262
40°	94516
45°	74406
50°	47997
55°	23558
60°	9683
65°	4247
70°	1226
75°	465
80°	337
85°	0



TEST NUMBER: P251176

CATALOG NUMBER: LSR8B60D010 EC8B60830 8LBS0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	362.3	5.4
10°-20°	1073.4	16.0
20°-30°	1661.9	24.8
30°-40°	1800.4	26.9
40°-50°	1295.6	19.3
50°-60°	433.5	6.5
60°-70°	65.5	1.0
70°-80°	5.6	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3097.7	46.2
0°-40°	4898.1	73.1
0°-60°	6627.1	98.9
0°-90°	6699.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6699.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3794	
5°	3794	362
15°	3798	1073
25°	3630	1662
35°	2902	1800
45°	1706	1296
55°	438	433
65°	58	66
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P251176

CATALOG NUMBER: LSR8B60D010 EC8B60830 8LBS0WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3794.4
2.5°	3794.4
5°	3794.4
7.5°	3796.3
10°	3798.3
12.5°	3802.2
15°	3798.3
17.5°	3782.8
20°	3747.9
22.5°	3695.5
25°	3629.6
27.5°	3524.9
30°	3362.0
32.5°	3148.7
35°	2902.5
37.5°	2636.9
40°	2348.0
42.5°	2037.8
45°	1706.2
47.5°	1347.5
50°	1000.5
52.5°	686.4
55°	438.2
57.5°	261.7
60°	157.0
62.5°	95.0
65°	58.2
67.5°	29.1
70°	13.6
72.5°	5.8
75°	3.9
77.5°	3.9
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)