

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247091

Luminaire Tested: **LSR8B90D010 EC8B909730 8LBWOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247091  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B90D010 EC8B909730 8LBW0LI  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7397.0 lumens  
Efficiency: N/A  
Efficacy: 85.9 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 86.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247091

CATALOG NUMBER: LSR8B90D010 EC8B909730 8LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P247091

CATALOG NUMBER: LSR8B90D010 EC8B909730 8LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P247091

CATALOG NUMBER: LSR8B90D010 EC8B909730 8LBW0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	404.4	5.5
10°-20°	1266.2	17.1
20°-30°	2002.5	27.1
30°-40°	2057.6	27.8
40°-50°	1276.4	17.3
50°-60°	361.8	4.9
60°-70°	24.4	0.3
70°-80°	3.3	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3673.1	49.7
0°-40°	5730.7	77.5
0°-60°	7368.9	99.6
0°-90°	7397.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7397.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4128	
5°	4192	404
15°	4479	1266
25°	4391	2002
35°	3336	2058
45°	1648	1276
55°	362	362
65°	15	24
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P247091

CATALOG NUMBER: LSR8B90D010 EC8B909730 8LBW0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4127.7
2.5°	4135.6
5°	4192.2
7.5°	4258.6
10°	4322.0
12.5°	4400.4
15°	4478.7
17.5°	4523.3
20°	4520.4
22.5°	4476.7
25°	4391.4
27.5°	4236.8
30°	3997.8
32.5°	3683.5
35°	3335.5
37.5°	2941.9
40°	2514.5
42.5°	2070.3
45°	1647.9
47.5°	1255.3
50°	900.3
52.5°	605.9
55°	361.9
57.5°	186.4
60°	81.3
62.5°	32.8
65°	14.8
67.5°	8.9
70°	5.9
72.5°	4.0
75°	3.0
77.5°	2.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)