

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250796

Luminaire Tested: **LSR8B60D010 EC8B60835 8LBW0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250796  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60835 8LBW0LI  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 3500 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6581.0 lumens  
Efficiency: N/A  
Efficacy: 110.6 lumens/watt  
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250796

CATALOG NUMBER: LSR8B60D010 EC8B60835 8LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P250796

CATALOG NUMBER: LSR8B60D010 EC8B60835 8LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	116762
5°	120216
10°	130233
15°	142493
20°	148243
25°	147702
30°	138542
35°	116174
40°	80886
45°	46326
50°	24879
55°	10263
60°	2553
65°	657
70°	325
75°	214
80°	320
85°	0



TEST NUMBER: P250796

CATALOG NUMBER: LSR8B60D010 EC8B60835 8LBW0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	379.7	5.8
10°-20°	1258.0	19.1
20°-30°	1979.4	30.1
30°-40°	1882.8	28.6
40°-50°	868.0	13.2
50°-60°	197.2	3.0
60°-70°	13.0	0.2
70°-80°	2.6	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3617.1	55.0
0°-40°	5499.9	83.6
0°-60°	6565.2	99.8
0°-90°	6581.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6581.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3786	
5°	3884	380
15°	4464	1258
25°	4341	1979
35°	3086	1883
45°	1062	868
55°	191	197
65°	9	13
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P250796

CATALOG NUMBER: LSR8B60D010 EC8B60835 8LBW0LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3786.5
1°	3784.7
2°	3791.9
3°	3813.5
4°	3845.9
5°	3883.7
6°	3930.5
7°	3981.0
8°	4033.2
9°	4094.4
10°	4159.2
11°	4224.0
12°	4292.4
13°	4357.3
14°	4416.7
15°	4463.5
16°	4497.7
17°	4521.1
18°	4531.9
19°	4530.1
20°	4517.5
21°	4495.9
22°	4468.9
23°	4432.9
24°	4391.5
25°	4341.1
26°	4281.6
27°	4206.0
28°	4116.0
29°	4011.6
30°	3890.9
32.5°	3529.0
35°	3086.1
37.5°	2571.1
40°	2009.4
42.5°	1485.4
45°	1062.3
47.5°	752.6
50°	518.6
52.5°	331.3
55°	190.9
57.5°	95.4
60°	41.4
62.5°	16.2
65°	9.0



TEST NUMBER: P250796

CATALOG NUMBER: LSR8B60D010 EC8B60835 8LBW0LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	5.4
70°	3.6
72.5°	3.6
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)