

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251334

Luminaire Tested: **LSR8B60D010 EC8B60840 8LBW0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251334
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60840 8LBW0B
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3944.0 lumens
Efficiency: N/A
Efficacy: 66.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251334

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBW0B

Luminous Intensity Polar Plot





TEST NUMBER: P251334

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBW0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77		83	79	76		81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71		78	74	70		76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56		65	60	56		64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49		57	52	49		57	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	111214
5°	108417
10°	105531
15°	103565
20°	100871
25°	97299
30°	89273
35°	68448
40°	32565
45°	12402
50°	6054
55°	2478
60°	617
65°	146
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P251334

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBW0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	330.2	8.4
10°-20°	912.9	23.1
20°-30°	1303.6	33.1
30°-40°	1080.3	27.4
40°-50°	266.4	6.8
50°-60°	47.9	1.2
60°-70°	2.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2546.7	64.6
0°-40°	3627.0	92.0
0°-60°	3941.3	99.9
0°-90°	3944.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3944.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3607	
5°	3502	330
15°	3244	913
25°	2860	1304
35°	1818	1080
45°	284	266
55°	46	48
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P251334

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBW0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	3606.6
2.5°	3576.6
5°	3502.5
7.5°	3430.4
10°	3370.3
12.5°	3312.2
15°	3244.1
17.5°	3164.0
20°	3073.9
22.5°	2971.8
25°	2859.7
27.5°	2707.5
30°	2507.2
32.5°	2224.8
35°	1818.3
37.5°	1313.7
40°	809.0
42.5°	470.6
45°	284.4
47.5°	188.2
50°	126.2
52.5°	82.1
55°	46.1
57.5°	22.0
60°	10.0
62.5°	4.0
65°	2.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)