

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244662

Luminaire Tested: **LD8B10D010 ER8B10827 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244662
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10827 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1034.0 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244662

CATALOG NUMBER: LD8B10D010 ER8B10827 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244662

CATALOG NUMBER: LD8B10D010 ER8B10827 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79		85	81	78		82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59		67	62	58		66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42		51	46	42		51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23106
5°	22643
10°	21925
15°	21629
20°	21501
25°	21228
30°	20089
35°	16567
40°	10345
45°	6650
50°	5157
55°	3973
60°	3010
65°	1955
70°	838
75°	405
80°	178
85°	106



TEST NUMBER: P244662

CATALOG NUMBER: LD8B10D010 ER8B10827 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	6.7
10°-20°	191.4	18.5
20°-30°	285.1	27.6
30°-40°	264.8	25.6
40°-50°	125.1	12.1
50°-60°	67.2	6.5
60°-70°	27.0	2.6
70°-80°	4.2	0.4
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	545.3	52.7
0°-40°	810.1	78.3
0°-60°	1002.4	96.9
0°-90°	1034.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1034.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	749	
5°	732	69
15°	678	191
25°	624	285
35°	440	265
45°	152	125
55°	74	67
65°	27	27
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P244662

CATALOG NUMBER: LD8B10D010 ER8B10827 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	749.3
2.5°	744.2
5°	731.5
7.5°	715.3
10°	700.2
12.5°	687.8
15°	677.5
17.5°	666.9
20°	655.2
22.5°	641.8
25°	623.9
27.5°	598.9
30°	564.2
32.5°	513.3
35°	440.1
37.5°	346.7
40°	257.0
42.5°	191.4
45°	152.5
47.5°	127.5
50°	107.5
52.5°	89.7
55°	73.9
57.5°	60.1
60°	48.8
62.5°	38.1
65°	26.8
67.5°	15.8
70°	9.3
72.5°	5.5
75°	3.4
77.5°	2.1
80°	1.0
82.5°	0.7
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)