

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251446

Luminaire Tested: **LSR8B60D010 EC8B60850 8LBN0MW**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251446  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60850 8LBN0MW  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 5000 CCT WITH MATTE WHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5818.0 lumens  
Efficiency: N/A  
Efficacy: 97.8 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251446

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBN0MW

### Luminous Intensity Polar Plot





TEST NUMBER: P251446

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBN0MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	188142
5°	186793
10°	170218
15°	145903
20°	129305
25°	115386
30°	93186
35°	64654
40°	41023
45°	30474
50°	26011
55°	22806
60°	20407
65°	18234
70°	15715
75°	14452
80°	13461
85°	11888



TEST NUMBER: P251446

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBN0MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	556.6	9.6
10°-20°	1287.4	22.1
20°-30°	1531.0	26.3
30°-40°	1082.3	18.6
40°-50°	558.6	9.6
50°-60°	383.0	6.6
60°-70°	248.6	4.3
70°-80°	130.4	2.2
80°-90°	40.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3375.0	58.0
0°-40°	4457.2	76.6
0°-60°	5398.9	92.8
0°-90°	5818.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5818.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6101	
5°	6034	557
15°	4570	1287
25°	3391	1531
35°	1718	1082
45°	699	559
55°	424	383
65°	250	249
75°	121	130
85°	34	37
90°	0	3
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251446

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBN0MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6101.3
2.5°	6101.3
5°	6034.5
7.5°	5812.6
10°	5436.2
12.5°	4987.3
15°	4570.3
17.5°	4227.1
20°	3940.4
22.5°	3669.2
25°	3391.3
27.5°	3042.6
30°	2617.1
32.5°	2159.3
35°	1717.5
37.5°	1323.3
40°	1019.1
42.5°	820.1
45°	698.8
47.5°	610.7
50°	542.2
52.5°	482.1
55°	424.2
57.5°	373.1
60°	330.9
62.5°	286.7
65°	249.9
67.5°	216.5
70°	174.3
72.5°	149.7
75°	121.3
77.5°	98.5
80°	75.8
82.5°	56.4
85°	33.6
87.5°	19.4
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251446

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBN0MW

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)