

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250800

Luminaire Tested: **LSR8B60D010 EC8B60850 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60850 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6665.9 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250800

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P250800

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118270
5°	121770
10°	131914
15°	144332
20°	150160
25°	149607
30°	140333
35°	117676
40°	81929
45°	46923
50°	25195
55°	10392
60°	2584
65°	664
70°	325
75°	214
80°	320
85°	0



TEST NUMBER: P250800

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	384.6	5.8
10°-20°	1274.3	19.1
20°-30°	2005.0	30.1
30°-40°	1907.2	28.6
40°-50°	879.2	13.2
50°-60°	199.8	3.0
60°-70°	13.1	0.2
70°-80°	2.6	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3663.8	55.0
0°-40°	5571.0	83.6
0°-60°	6649.9	99.8
0°-90°	6665.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6665.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3835	
5°	3934	385
15°	4521	1274
25°	4397	2005
35°	3126	1907
45°	1076	879
55°	193	200
65°	9	13
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P250800

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3835.4
1°	3833.6
2°	3840.9
3°	3862.8
4°	3895.6
5°	3933.9
6°	3981.3
7°	4032.4
8°	4085.3
9°	4147.3
10°	4212.9
11°	4278.6
12°	4347.9
13°	4413.5
14°	4473.7
15°	4521.1
16°	4555.8
17°	4579.5
18°	4590.5
19°	4588.6
20°	4575.9
21°	4554.0
22°	4526.6
23°	4490.1
24°	4448.2
25°	4397.1
26°	4336.9
27°	4260.3
28°	4169.2
29°	4063.4
30°	3941.2
32.5°	3574.6
35°	3126.0
37.5°	2604.4
40°	2035.3
42.5°	1504.6
45°	1076.0
47.5°	762.3
50°	525.2
52.5°	335.6
55°	193.3
57.5°	96.7
60°	41.9
62.5°	16.4
65°	9.1



TEST NUMBER: P250800

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	5.5
70°	3.6
72.5°	3.6
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)