

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246468

Luminaire Tested: **LD8B10D010 ER8B10830 8LBS0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246468
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10830 8LBS0B
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1003.0 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246468

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBS0B

Luminous Intensity Polar Plot





TEST NUMBER: P246468

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBS0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	94	90	103	98	93	89	94	90	87		91	88	85		88	86	84	82
3	98	90	84	79	96	89	83	79	86	81	77		84	80	76		81	78	75	73
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75	71	67	66
5	86	75	68	63	84	74	68	63	72	66	62		71	65	61		69	64	61	59
6	80	69	62	56	78	68	61	56	67	60	56		65	60	55		64	59	55	53
7	75	63	56	51	73	63	56	51	61	55	51		60	54	50		59	54	50	48
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		54	49	46	44
9	66	54	47	42	65	54	47	42	53	46	42		52	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	17916
5°	17898
10°	17804
15°	17673
20°	17477
25°	17203
30°	16700
35°	15912
40°	14737
45°	12368
50°	8175
55°	4037
60°	1603
65°	620
70°	99
75°	0
80°	0
85°	0



TEST NUMBER: P246468

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBS0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.9	5.5
10°-20°	156.1	15.6
20°-30°	232.3	23.2
30°-40°	263.1	26.2
40°-50°	212.7	21.2
50°-60°	73.8	7.4
60°-70°	10.1	1.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	443.2	44.2
0°-40°	706.3	70.4
0°-60°	992.8	99.0
0°-90°	1003.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1003.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	581	
5°	578	55
15°	554	156
25°	506	232
35°	423	263
45°	284	213
55°	75	74
65°	8	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246468

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBS0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	581.0
2.5°	580.3
5°	578.2
7.5°	573.9
10°	568.6
12.5°	561.5
15°	553.6
17.5°	543.7
20°	532.6
22.5°	519.8
25°	505.6
27.5°	488.5
30°	469.0
32.5°	446.9
35°	422.7
37.5°	396.0
40°	366.1
42.5°	329.5
45°	283.6
47.5°	228.1
50°	170.4
52.5°	116.7
55°	75.1
57.5°	44.5
60°	26.0
62.5°	15.3
65°	8.5
67.5°	3.9
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)