

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251124

Luminaire Tested: **LSR8B60D010 EC8B60927 8LBW0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251124  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P200903)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60927 8LBW0WH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 2700 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5044.4 lumens  
Efficiency: N/A  
Efficacy: 84.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.11  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251124

CATALOG NUMBER: LSR8B60D010 EC8B60927 8LBW0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P251124

CATALOG NUMBER: LSR8B60D010 EC8B60927 8LBW0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78	75	72	70
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73	69	66	64
6	83	73	67	62	82	73	66	62	71	65	61		69	64	61		68	64	60	59
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64	59	55	54
8	74	63	57	52	73	63	56	52	62	56	52		61	55	51		59	55	51	50
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	55	49	45	65	55	49	44	54	48	44		53	48	44		52	48	44	43

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P251124

CATALOG NUMBER: LSR8B60D010 EC8B60927 8LBW0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	330.2	6.5
10°-20°	1016.2	20.1
20°-30°	1490.8	29.6
30°-40°	1317.0	26.1
40°-50°	674.6	13.4
50°-60°	188.6	3.7
60°-70°	24.1	0.5
70°-80°	2.5	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2837.2	56.2
0°-40°	4154.2	82.4
0°-60°	5017.4	99.5
0°-90°	5044.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5044.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3305	
5°	3393	330
15°	3615	1016
25°	3288	1491
35°	2118	1317
45°	853	675
55°	192	189
65°	13	24
75°	0	2
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251124

CATALOG NUMBER: LSR8B60D010 EC8B60927 8LBW0WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3304.6
2.5°	3317.3
5°	3393.0
7.5°	3496.6
10°	3575.1
12.5°	3613.4
15°	3614.7
17.5°	3578.4
20°	3516.4
22.5°	3418.3
25°	3287.8
27.5°	3093.2
30°	2811.8
32.5°	2478.5
35°	2118.4
37.5°	1767.5
40°	1447.4
42.5°	1145.5
45°	853.4
47.5°	609.1
50°	419.5
52.5°	293.2
55°	192.5
57.5°	122.2
60°	72.9
62.5°	37.8
65°	12.7
67.5°	8.2
70°	7.1
72.5°	4.2
75°	0.0
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251124

CATALOG NUMBER: LSR8B60D010 EC8B60927 8LBW0WH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)