

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244896

Luminaire Tested: **LD8B10D010 ER8B10840 8LBS0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244896
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10840 8LBS0WMH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1204.0 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244896

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBS0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244896

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBS0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86		90	87	85		88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76		83	79	75		80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61		70	64	60		68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55		64	58	54		63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49		59	53	49		58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38		47	42	38		46	41	37	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21049
5°	20984
10°	20797
15°	20591
20°	20368
25°	20047
30°	19498
35°	18608
40°	17245
45°	14561
50°	9988
55°	5511
60°	2769
65°	1561
70°	847
75°	608
80°	391
85°	248



TEST NUMBER: P244896

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBS0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.3	5.3
10°-20°	181.9	15.1
20°-30°	270.8	22.5
30°-40°	307.6	25.6
40°-50°	251.4	20.9
50°-60°	98.5	8.2
60°-70°	23.0	1.9
70°-80°	5.5	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	517.0	42.9
0°-40°	824.6	68.5
0°-60°	1174.6	97.6
0°-90°	1204.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1204.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	683	
5°	678	64
15°	645	182
25°	589	271
35°	494	308
45°	334	251
55°	102	99
65°	21	23
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P244896

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBS0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	682.6
2.5°	681.6
5°	677.9
7.5°	671.8
10°	664.2
12.5°	654.8
15°	645.0
17.5°	633.4
20°	620.7
22.5°	605.9
25°	589.2
27.5°	569.7
30°	547.6
32.5°	522.6
35°	494.3
37.5°	463.2
40°	428.4
42.5°	386.4
45°	333.9
47.5°	272.3
50°	208.2
52.5°	149.6
55°	102.5
57.5°	67.0
60°	44.9
62.5°	30.8
65°	21.4
67.5°	14.1
70°	9.4
72.5°	6.5
75°	5.1
77.5°	3.6
80°	2.2
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)