

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250878

Luminaire Tested: **LSR8B60D010 EC8B60935 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250878
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60935 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5996.0 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250878

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P250878

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88	91	88	86	88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63	71	66	62	69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47	56	51	46	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103089
5°	103535
10°	105218
15°	107878
20°	109761
25°	109884
30°	106485
35°	97495
40°	84731
45°	67045
50°	43478
55°	21725
60°	9121
65°	4013
70°	1244
75°	620
80°	604
85°	601



TEST NUMBER: P250878

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBS0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.8	5.3
10°-20°	954.9	15.9
20°-30°	1479.3	24.7
30°-40°	1606.5	26.8
40°-50°	1167.4	19.5
50°-60°	396.8	6.6
60°-70°	63.2	1.1
70°-80°	6.8	0.1
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2753.9	45.9
0°-40°	4360.4	72.7
0°-60°	5924.6	98.8
0°-90°	5996.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5996.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3343	
5°	3345	320
15°	3379	955
25°	3230	1479
35°	2590	1607
45°	1537	1167
55°	404	397
65°	55	63
75°	5	7
85°	2	1
90°	0	



TEST NUMBER: P250878

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBS0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3343.1
2.5°	3343.1
5°	3344.8
7.5°	3350.0
10°	3360.3
12.5°	3372.3
15°	3379.2
17.5°	3372.3
20°	3344.8
22.5°	3294.9
25°	3229.6
27.5°	3131.6
30°	2990.6
32.5°	2803.1
35°	2589.9
37.5°	2357.7
40°	2104.9
42.5°	1831.5
45°	1537.4
47.5°	1221.0
50°	906.3
52.5°	620.8
55°	404.1
57.5°	245.9
60°	147.9
62.5°	91.1
65°	55.0
67.5°	31.0
70°	13.8
72.5°	8.6
75°	5.2
77.5°	3.4
80°	3.4
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0

(END OF REPORT)