

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245544

Luminaire Tested: **LD8B10D010 ER8B10840 8LBW0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245544  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B10D010 ER8B10840 8LBW0GPH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 4000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1010.1 lumens  
Efficiency: N/A  
Efficacy: 99.0 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245544

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBW0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245544

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBW0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66		74	70	66		73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		65	59	56		63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51		60	55	51		59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48		57	51	47		56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52	47	44	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	24250
5°	23677
10°	22936
15°	22602
20°	22337
25°	21857
30°	20474
35°	16718
40°	9979
45°	5996
50°	4322
55°	2941
60°	1844
65°	905
70°	234
75°	83
80°	71
85°	0



TEST NUMBER: P245544

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBW0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.0	7.1
10°-20°	199.8	19.8
20°-30°	293.4	29.1
30°-40°	266.0	26.3
40°-50°	113.9	11.3
50°-60°	50.4	5.0
60°-70°	13.5	1.3
70°-80°	1.1	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	565.2	56.0
0°-40°	831.2	82.3
0°-60°	995.5	98.6
0°-90°	1010.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1010.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	786	
5°	765	72
15°	708	200
25°	642	293
35°	444	266
45°	138	114
55°	55	50
65°	12	13
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P245544

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBW0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	786.4
2.5°	780.2
5°	764.9
7.5°	747.4
10°	732.5
12.5°	720.1
15°	708.0
17.5°	695.3
20°	680.7
22.5°	663.6
25°	642.4
27.5°	614.0
30°	575.0
32.5°	520.3
35°	444.1
37.5°	344.2
40°	247.9
42.5°	179.0
45°	137.5
47.5°	110.8
50°	90.1
52.5°	71.5
55°	54.7
57.5°	40.8
60°	29.9
62.5°	20.8
65°	12.4
67.5°	5.5
70°	2.6
72.5°	1.5
75°	0.7
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)